FERGUSON®
FACILITIES SUPPLY

FEATURES

- Energy Savings of up to 83%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Steel Trim in Oil Rubbed Bronze Finish
- Die Formed of 22 Gauge Plated Steel
- Replaces 60W Incandescent
- ADA Approved

OPTICS
- Acrylic White Lens

APPLICATIONS
- Hallways
- Corridors
- Bathrooms
- Lobbies

CERTIFICATIONS
- UL/cUL Listed
- Energy Star
- Lighting Facts

SPECIFICATIONS

Part Number: LED15011A-34

Manufacturer Limited Warranty:	3 Years	**Certifications:**	UL Listed
Kelvin Temperature (CCT):	3000K	**DLC Listed:**	No
Wattage:	10.2W	**Average Hour Life:**	50,000 hrs
Lumens:	889 lm	**Max. Ambient Temperature:**	45°C
Efficacy:	92.8 lm/w	**Min. Ambient Temperature:**	-20°C
CRI:	80	**Power Factor:**	>0.9
Input Voltage	DC 120V	**THD:**	<20%

TECHNICAL

Weight:	2.77 lbs	**Product Width:**	7''
Length:	3.5	**LED Beam Angel:**	120
Product Height:	9.75''	**LED Type:**	Integrated LED Array

c **UL** us
LISTED

LED lighting facts
A Program of the U.S. DOE

ENERGY STAR

Specifications subject to change without notice

FERGUSON®
FACILITIES SUPPLY

LINE DRAWINGS

87 [3 3/8]

178 [7]

250 [9 7/8]

LIGHTING FACTS

Cordelia Lighting

LED lighting facts®
A Program of the U.S. DOE

Light Output (Lumens)	**889**
Watts	**9.58**
Lumens per Watt (Efficacy)	**92.8**

Color Accuracy Color Rendering Index (CRI)	**83**

Light Color
Correlated Color Temperature (CCT)   **3000 (Bright White)**

Warm White	Bright White	Daylight
2700K	3000K	4500K	6500K

All results are according to IESNA LM-79-2008: *Approved Method for the Electrical and Photometric Testing of Solid-State Lighting.* The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the *Label Reference Guide.*

Registration Number: ZMBK-1F33VS (1/17/2017)
Model Number: LED15011A-##
Type: Luminaire - Decorative

Specifications subject to change without notice