



# Crown Molding Wood Frame KCM/WCM/CCM/UCM

## Specifications:

### Features

Contoured sloped sided crown molding ceiling mount fixture is available in three sizes, 13-1/2" x 51-3/8", 18-1/8" x 51-3/8" and 27-3/4" x 27-3/4" and four finishes, white, oak, cherry, or unfinished. It can be used in various applications including corridors, kitchens and public spaces. This product offers a flush to ceiling solid wood frame with a lift and shift gravity retention matt white diffuser. Fixture mounts to standard junction box (not included).

### Construction

Housing is die-formed of 22-gauge steel. Standard mounting holes are included. Decorative crown molding frame assembly is constructed of solid wood. Power supply connections can be made inside the fixture wiring compartment or in the junction box (not included).

### Finish

Back plate is finished in lighting grade white baked gloss enamel paint. Frame exterior is painted stained medium oak, white, cherry, or unfinished.

### Diffuser

Acrylic diffuser is .080" thick matte white.

### Electrical

This unit is wired with UL listed instant start electronic normal power factor ballast for 120V/60 Hz AC operation.

### Lamping

For use with 2/32 or 4/32 watt T8 linear fluorescent lamps or 32 watt T8 U lamps with 6" spacing; supplied by others.

### Certification


All fixtures are cULus listed for damp locations.

### Options (consult factory)

120-277V HPF  
Dimming  
Clear prismatic acrylic diffuser

Specifications and dimensions  
subject to change without notice.

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number



## Ordering Information:

Model No.				Lamps		Dimensions			Mounting
Oak	White	Cherry	Unfinished	Qty	Lamp	H	W	L	M
KCM232R8	WCM232R8	CCM232R8	UCM232R8	2	F32T8	3-3/8"	13-1/2"	51-3/8"	43-3/4"
KCM2U3R8	WCM2U3R8	CCM2U3R8	UCM2U3R8	2	FB32T8	3-3/8"	27-3/4"	27-3/4"	21"
KCM432R8	WCM432R8	CCM432R8	UCM432R8	4	F32T8	3-3/8"	18-1/4"	51-3/8"	43-3/4"