M18 FUEL

HOLE HAWG® 1/2" Right Angle Drill Kit

2707-22HD, 2707-22 (2707-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	1/2" All Metal Chuck
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length / Weight	17.0" / 9.8 lbs

Includes: **2707-22HD** (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; **2707-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger;
All Kits Include: Chuck Key, Carrying Case

M18 FUEL

HOLE HAWG® Right Angle Drill Kit w/ QUIK-LOK™

2708-22HD, 2708-22 (2708-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length / Weight	17.0" / 9.3 lbs

Includes: **2708-22HD** (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; **2708-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger;
All Kits Include: Carrying Case

M18 FUEL

SUPER HAWG™ 1/2" Right Angle Drill Kit

2809-22 (2809-20 Tool-Only)

REDLITHIUM HIGH OUTPUT XC6.0

Specifications:

RPM	0 – 1,550
Chuck Type	1/2" All Metal Chuck
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6-1/4"
Mechanical Clutch	In Low Speed
Length / Weight	20.5" / 14.4 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC6.0 Battery Packs, Side Handle, Chuck Key, Rapid Charger, Contractor Bag

M18 FUEL

SUPER HAWG™ Right Angle Drill Kit w/ QUIK-LOK™

2811-22 (2811-20 Tool-Only)

REDLITHIUM HIGH OUTPUT XC6.0

Specifications:

RPM	0 – 1,550
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6-1/4"
Mechanical Clutch	In Low Speed
Length / Weight	20.5" / 14.9 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC6.0 Battery Packs, Side Handle, Rapid Charger, Contractor Bag

M18 FUEL

1-1/2" Magnetic Drill Kit

2787-22HD

REDLITHIUM HIGH OUTPUT XC8.0

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13.8" x 7.5" x 15.5"
Weight	30.5 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, Rapid Charger, Carrying Case

M18 FUEL

1-1/2" Lineman Magnetic Drill Kit

2788-22HD

REDLITHIUM HIGH OUTPUT XC8.0

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13.8" x 7.5" x 15.5"
Weight	30.4 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, 12V Inverter, Rapid Charger, Carrying Case

M18 FUEL

1-3/4" SDS Max Rotary Hammer w/ ONE-KEY™ Kit

2718-22HD, 2718-21HD (2718-20 Tool-Only)

SDS MAX

REDLITHIUM HIGH OUTPUT HD12.0

Specifications:

Impact Energy	8.1 ft-lbs
RPM	0 – 380
BPM	0 – 2,900
Clutch	AUTOSTOP™ E-Clutch
Vibration	10 m/s²
2-Mode Operation	Rotary Hammer & Hammer Only
Weight	19.7 lbs

Includes: **2718-22HD** (2) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Packs; **2718-21HD** (1) M18™ REDLITHIUM™ HIGH OUTPUT™ HD12.0 Battery Pack;
All Kits Include: Side Handle, Grease Tube, Rapid Charger, Carrying Case

M18 FUEL

1-9/16" SDS Max Rotary Hammer Kit

2717-22HD (2717-20 Tool-Only)

SDS MAX

REDLITHIUM HIGH OUTPUT XC8.0

Specifications:

RPM	0 – 440
BPM	0 – 3,000
Impact Energy	5.0 ft-lbs
2-Mode Operation	Rotary Hammer and Hammer Only
Weight	13.8 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH OUTPUT™ XC8.0 Battery Packs, Side Handle, Depth Rod, Rapid Charger, Carrying Case

Related Accessory:
2306-22 M12™ HAMMERVAC™ Universal Dust Extractor

M18 FUEL

1-1/8" SDS Plus Rotary Hammer Kit

2715-22HD, 2715-22, 2715-22DE (2715-20 Tool-Only)

SDS PLUS

Specifications:

RPM	0 – 1,350
BPM	0 – 5,000
Impact Energy	3.3 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	10.1 lbs

Includes: **2715-22HD** (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; **2715-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger; **2715-22DE** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger;
All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ HAMMERVAC™ Dedicated Dust Extractor

COMPLIANCE OSHA SOLUTION | CERTIFIED HEPA FILTER | TABLE 1 COMPLIANCE

2715-DE

Specifications:

Compatibility	For use with 2715-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"

Includes: Replacement Nozzle and HEPA Filter

M18 FUEL

1" SDS Plus Rotary Hammer Kit

2712-22, 2712-22DE (2712-20 Tool-Only)

SDS PLUS

Specifications:

RPM	0 – 1,400
BPM	0 – 4,900
Impact Energy	1.7 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	9.4 lbs

Includes: **2712-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger; **2712-22DE** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger;
All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ HAMMERVAC™ Dedicated Dust Extractor

COMPLIANCE OSHA SOLUTION | CERTIFIED HEPA FILTER | TABLE 1 COMPLIANCE

2712-DE

Specifications:

Compatibility	For use with 2712-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"

Includes: Replacement Nozzle and HEPA Filter

M18 FUEL

1" SDS Plus D-Handle Rotary Hammer Kit

2713-22HD, 2713-22 (2713-20 Tool-Only)

SDS PLUS

Specifications:

Capacity	1"
Impact Energy	2.15 ft-lbs
RPM	0 – 1,500
BPM	0 – 4,400
Length / Weight	16.5" / 8.5 lbs

Includes: **2713-22HD** (2) M18™ REDLITHIUM™ HD9.0 Battery Packs, Rapid Charger; **2713-22** (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Multi-Voltage Charger;
All Kits Include: Side Handle, Depth Rod, Carrying Case

M18™ 7/8" SDS Plus Rotary Hammer Kit

2605-22 (2605-20 Tool-Only)

SDS PLUS

Specifications:

RPM	0 – 1,400
BPM	0 – 4,800
Impact Energy	1.4 ft-lbs
3-Mode Operation	Hammer Only, Rotary Hammer and Rotation Only
Weight	7.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC3.0 Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

Related Accessory:
2306-22 M12™ HAMMERVAC™ Universal Dust Extractor

M18™ 5/8" SDS Plus Rotary Hammer Kit

2612-22, 2612-21 (2612-20 Tool-Only)

SDS PLUS

Specifications:

RPM	0 – 1,300
BPM	0 – 7,000
Impact Energy	1.0 ft-lbs
2-Mode Operation	Rotary Hammer and Rotation Only
Weight	5.5 lbs

Includes: **2612-22** (2) M18™ REDLITHIUM™ XC3.0 Battery Packs; **2612-21** (1) M18™ REDLITHIUM™ XC3.0 Battery Pack;
All Kits Include: Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

Related Accessory:
2306-22 M12™ HAMMERVAC™ Universal Dust Extractor