Specifications

PFWSC8852 ORRS SINGLE HANDLE LAVATORY FAUCET



Product Features ·Ceramic cartridge


- · Metal lever handle
- · With brass pop-up
- Max. flow rate 1.2 gpm (4.54 L/min) at 60 psi
- Meets ASME A112.18.1
- · NSF 61 compliant
- · cUPC/IAPMO listed
- · EPA WaterSense Certified
- · ADA Compliant

Model Numbers:

PFWSC8852CP	Chrome
PFWSC8852BN	Brushed nickel
PFWSC8852MB	Matte black

Optional Parts


0BPF15Y0261500*	Deck plate
PFXAER05	0.5gpm aerator insert





PFWSC8852CP

Product Specifications





FERGUSON.COM/PROFLO

* All measurements are nominal. Please verify before actual installation.

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. This product meets ASME: A112.18.1. *Compliant with lead content requirements of US Senate Bill S.3874.*