SPECIFICATIONS

AMALFI™ SINGLE HANDLE PRESSURE BALANCE TUB & SHOWER TRIM KIT

Model

D520030T (Tub & Shower trim)
D520530T (Shower only trim)
D510430T(Valve only trim)

Description

- 4 1/2" Mono Chic® showerhead D460158
- 6" metal showerarm
- Metal lever handle
- Thread/slip fit
- Diverter on spout
- Use with valve D1120 series (w/stops) or D1150 series (w/o stops) or D1125 series (w/stops) or D1155 series (w/o stops)
- 2.5gpm (9.5L/min) maximum flow rate @ 80 psi

Flow Rate



D520030T (shown)

Standards

- UPC/cUPC
- ASME A112.18.1M/ A112.18.1
- ADA Accessibility Guidelines for Buildings and Facilities - 309.4 Operation for Operable Parts

Finishes Available

ÆChrome
ÆOther: Refer to Price List for additional finish

Warranty

Danze products are covered by a manufacturer's limited "lifetime" warranty for manufacturing defects.









Submittal Information:

Job Name: _____ *Location:* _____

Contractor: _____ *Contact #:* _____