SPECIFICATIONS

LOGAN SQUARE™ TRIM ONLY SINGLE HANDLE PRESSURE BALANCE TUB & SHOWER FAUCET

Model

D500036T (Tub & Shower trim)
D500036LST (Tub & Shower trim,less showerhead)
D500536T (Shower only trim)
D500536LST (Shower only trim,less showerhead)
D510436T(Valve only trim)

Flow Rate



D500036T (shown)

Description

- Square showerhead D460049, 2.5gpm (9.5L/min) maximum flow rate @ 80 psi
- 6" metal showerarm
- Metal lever handle
- Diverter on spout
- Use with valve: D1120 series (w/ stops) or D1150 series (w/o stops) or D1125 series (w/ stops) or D1155 series (w/o stops)

Standards

- UPC/Cupc
- Energy Policy Act of 1992

MEETS ASME A112.18.1M/ A112.18.1

- ASME A112.18.1M/ A112.18.1

- ADA Accessibility Guidelines for Buildings and Facilities - 4.27.4 Controls and Mechanisms

Finishes Available

- Chrome
- Other: Refer to Price List for additional finish

Warranty

Danze products are covered by a manufacturer's limited "lifetime" warranty for manufacturing defects.







Submittal Information:

Job Name: _____ *Location:* _____

Contractor: _____ *Contact #:* _____