



Job Name:

Job Type:

Comments:

Quantity:

**77625-962: Semi-Flush Convertible Fixture**



**Dimensions:**

**Diameter:** 12 1/2"

**Height Flush:** 12 1/4"

**Height:** 15 3/4"

**Height w/ Chain:** 139 3/4"

**Wire:** 144" (color/Clear)

**Chain:** 120"

**Mounting Proc.:** Dual Mount

**Connection:** Mounted To Box

**Bulbs:**

- 2 - medium A - Line 100w Max. 120v - Not included
- 2 - LED Medium LED A-19 8w 120v - Not included
- 2 - LED Medium LED A-19 13.5w 120v - Not included

**Features:**

- Fixture is dual mount and may be installed flush or as a pendant
- Supplied with 12' of Wire Pre-laced through 10' of Chain

**Material List:**

- 1 Body - Steel - Brushed Nickel
- 1 Chain - Steel - Brushed Nickel

**Safety Listing:**

- UL Listed for Dry Locations
- cUL Listed for Dry Locations

**Instruction Sheets:**

- English (HC-1565)
- French (F-004)

**Collection:** Wheaton

Semi-Flush Convertible Fixture in Brushed Nickel Finish with Satin Etched Glass Shade

**UPC #:**785652756047

**Finish:** Brushed Nickel (962)

**Shade / Glass / Diffuser Details:**

| Part  | Material | Finish       | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|--------------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass    | Satin Etched | 1        |             |        |       | 4 9/16 | 12 7/16  | 7/16            |                  |                 |                    |

**Backplate / Canopy Details:**

| Type   | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|--------|-----------------|-------|-------|----------|---------------|-----------------|
| Canopy |                 |       | 1 1/8 | 5 1/2    |               |                 |

**Replacement Bulb Data:**

| Product # | Type | Base        | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S    | A-19 | E-26 Medium |       |                | 120v  | 50000 | 425    | 3000      | 85  |
| 97309S    | A-19 | E-26 Medium |       |                | 120v  | 50000 | 850    | 3000      | 85  |

**Shipping Information:**

| Package Type | Product # | Quantity | UPC          | Length | Width | Height | Cube  | Weight | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|-------|--------|----------|
| Individual   | 77625-962 | 1        | 785652756047 | 15.25  | 15.25 | 12.25  | 1.649 | 9.6    | Yes      |
| NJ Pallet    |           | 46       |              | 48     | 40    | 72     | 80    | 441.6  | No       |
| NV Pallet    |           | 32       |              | 48     | 40    | 72     | 80    | 307.2  | No       |