



Job Name:

Job Type:

Comments:

Quantity:

44941-962: Three Light Wall/Bath

Dimensions:

Width: 24 1/4"

Extends: 8"

Height: 8 1/4"

Wire: 6 1/2"

Mounting Proc.: Wall / Bath

Connection: Mounted To Box



Bulbs:

- 3 - medium A-19 100w Max. 120v - Not included
- 3 - LED Medium LED A-19 8w 120v - Not included
- 3 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

ETL Listed for Damp Locations
cETL Listed for Damp Locations

Collection: Windgate

Three Light Wall/Bath in Brushed Nickel Finish with Alabaster Glass Shades

UPC #:785652020230

Finish: Brushed Nickel (962)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Alabaster	3				4 3/8	5 7/16	1 5/8			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	0	24 1/8	7/8	0	3 1/4	5

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	44941-962	1	785652020230	27	9	9	1.266	7.4	Yes
NJ Pallet		48		48	40	75.75	84.167	355.2	No
NV Pallet		48		48	40	75.75	84.167	355.2	No