



Job Name:

Job Type:

Comments:

Quantity:

44062-05: Three-Light Sussex Wall/Bath

Dimensions:

Width: 24"

Extends: 10 1/4"

Height: 10 1/4"

Wire: 6 1/2"

Mounting Proc.: Cap Nuts

Connection: Mounted To Box



Bulbs:

- 3 - medium A - Line 100w Max. 120v - Not included
- 3 - LED Medium LED A-19 8w 120v - Not included
- 3 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Body - Steel - Chrome

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Collection: Sussex

Three Light Decorative Bath Bracket in Chrome Finish with Satin White Glass Shades.

UPC #:785652440632

Finish: Chrome (05)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Satin White	3				4 1/16	7 1/2	1 11/16			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			3	6 5/8	7	3 1/4

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	44062-05	1	785652440632	21.5	9.5	9	1.064	9.46	Yes
NJ Pallet		56		48	40	77	85.556	529.76	No
NV Pallet		56		48	40	74.25	82.5	548.81	No