



Job Name:

Job Type:

Comments:

Quantity:

44147-814: Four-Light Acadia Wall Light

Dimensions:

Width: 30 1/2"

Extends: 8 1/4"

Height: 10 1/2"

Wire: 6 1/2"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box



Bulbs:

- 4 - medium A - Line 100w Max. 120v - Not included
- 4 - LED Medium LED A-19 8w 120v - Not included
- 4 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Arms - Steel - Misted
Bronze

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Instruction Sheets:

English (HC-696)
French (F-010)

Collection: Acadia

Four Light Bath Bar In Misted Bronze Finish with Champagne
Seeded Glass Shades with Misted Bronze Trim

UPC #:785652441479

Finish: Misted Bronze (814)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Champagne Seeded	1					6 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	5 1/2	11	1		5	5 1/2

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	44147-814	1	785652441479	35	11	12	2.674	10.55	Yes
NJ Pallet		24		48	40	72	80	252	No
NV Pallet		24		48	40	72	80	253.2	No