


EZT PRO FEATURES & SPECIFICATIONS





FEATURES AND SPECIFICATIONS:

- 1 HIGH STRENGTH STRUCTURAL CARBON STEEL WELDED "TEE" HANDLE FINISHED WITH DURABLE BLUE POWDER COAT. OFFERED IN 3 STANDARD LENGTHS VIA FERGUNSONS/POLLARDWATER P/N'S:
 - P/N EPROBLU3L: LENGTH: 3 FT 2" (38"); WEIGHT: 4 LBS 6 OZS (70 OZS)
 - P/N EPROBLU5L: LENGTH: 5 FT 2" (62"); WEIGHT: 6 LBS 2 OZS (98 OZS)
 - P/N EPROBLU6L: LENGTH: 6 FT 8" (80"); WEIGHT: 7 LBS 4 OZS (116 OZS)
- 2 STAINLESS STEEL TOOL HEAD MOUNTING HARDWARE.
- 3 PRECISION MACHINED HIGH STRENGTH ALUMNINUM PATENT-PENDING "EZT TOOL HOUSING" FEATURES:
 - MIN PORT SIZE: 2" PORT (1 15/16" MAX TOOL DIA)
 - TORQUE: TRANSMITS 80 TO 200 FT-LBS (SEE TORQUE SPEC DETAIL)
 - ANTI STICTION FEATURE: PREVENTS "STICTIION" DUE TO AIR, WATER AND MUD IN 2" PORTS
- 4 EXTENDED HARDENED STAINLESS STEEL PINS AND STAINLESS STEEL SPRINGS (NOT SHOWN)
 - 1. HIGH STRENGTH TRANSMITS TORQUES UP TO 200 FOOT-POUNDS
 - 2. HIGH COMPLIANCE WILL CONFORM AROUND MOST COMMON WATER VALVE KNOBS INCLUDING:
 - STOP AND WASTE
 - QUARTER ANGLE
 - CORP STOPS
 - CROSSED KNOB
 - BROKEN KNOBS
 - METER LID PENTA NUTS
 - 3. EXTENDED PINS ENABLES EZT TOOL HEAD TO ENGAGE VALVE KNOBS BY EDGE DRAMATACILLY EXTENDING RANGE OF ENGAGEMENT, REDUCTION OF TRAIL AND ERROR IN DIFFICULT INSTALLATIONS AND THUS "SAVES THE FISHING FOR THE LAKE"

EZT TORQUE SPECIFCATION/RATING

THE TOOL TORQUE RATING VARIES FROM 80 TO 200 FOOT-POUNDS DEPENDING ON TOOL ENGAGEMENT WITH THE VALVE KNOB. THE ILLUSTRATIONS BELOW SHOW THE RANGE OF EXPECTED TOOL TO VALVE KNOB ENGAGEMENT AND CORESPONDING TOQUE RATING.

CENTER ENGAGEMENT: 200 FT-LBS
TOOL ENGAGES VALVE KNOB THROUGH CENTER MAXIMIZING PINS ENGAGED.



EDGE ENGAGEMENT: 80 FT-LBS
TOOL ENGAGES VALVE KNOB EDGE MINIMIZING PINS ENGAGED.

