

**Line Voltage Direct Wire  
EXD120/220/320/420**

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number

**Features**

This is the most economical product of the xenon family. Housing is 1-5/16" deep by 4" wide, is available in various lengths and includes a high/low switch. The line voltage unit includes 20 watt lamps and is used for direct wire applications. Specular reflector provides maximum light output. Dimmable with standard wall dimmer and includes a BX and NM cable connector. Quick wire connectors allow for easy hard wire installation. Full size knock outs are located on the top and back. Applications include kitchens, study areas and displays.

**Construction**

Housing is die-formed of 22-gauge steel. Separate hingeable service tray allows for easy installation and snaps into position without hardware. Power connections are made inside service tray.

**Finish**

All exposed metal parts are post painted lighting grade white gloss enamel paint or applied oil-rubbed bronze.

**Diffuser**

Clear tempered textured glass is .100" thick and slides into housing.

**Electrical**

This unit is wired for 120V operation. High/low switch included.


**Lamping**

For use with 20 watt 120V G8 bi-pin xenon lamps included. Lamps are rated for 5,000 hours.

**Certification**

Fixtures are cULus listed for damp locations and carry a UL rating for undercabinet mounting.

**Specifications and dimensions**  
subject to change without notice.



**Ordering Information:**

Model No.	Finish	120V	Lamps		Dimensions			Mounting
			Qty	Lamp	H	W	L	M
White	EXD120WH	1	20W BI-PIN BASE	1-5/16"	4"	9"	5-7/8"	
White	EXD220WH	2	20W BI-PIN BASE	1-5/16"	4"	12"	9-1/8"	
White	EXD320WH	3	20W BI-PIN BASE	1-5/16"	4"	18"	15-1/8"	
White	EXD420WH	4	20W BI-PIN BASE	1-5/16"	4"	24"	21-1/8"	
Oil-Rubbed bronze	EXD120RB	1	20W BI-PIN BASE	1-5/16"	4"	9"	5-7/8"	
Oil-Rubbed bronze	EXD220RB	2	20W BI-PIN BASE	1-5/16"	4"	12"	9-1/8"	
Oil-Rubbed bronze	EXD320RB	3	20W BI-PIN BASE	1-5/16"	4"	18"	15-1/8"	
Oil-Rubbed bronze	EXD420RB	4	20W BI-PIN BASE	1-5/16"	4"	24"	21-1/8"	