


# Line Voltage Linkable & Direct Wire EXL120/220/320/420

# **Features**

All purpose xenon undercabinet light with a compact design and low profile. The housing is 1-5/16" deep by 4" wide, is available in various lengths and includes a high/low switch. The line voltage unit includes 20 watt lamps and is linkable or direct wire. Specular reflector provides maximum light output. Dimmable with standard wall dimmer. Accessories include a 5'3 wire cord and plug, 12" connecting cable and BX and NM cable connector. Quick wire connectors allow for easy hard wire installation. Full size knock outs are located on the top and back. Ends include connector for linkable system up to 560 watts. Applications include kitchens, study areas and displays.





## Construction

Housing is die-formed of 22-gauge steel. Separate hingeable service tray allows for easy installation and snaps into position without hardware. Power connections are made inside service tray or with included cord and plug.

## **Finish**

All exposed metal parts are post painted lighting grade white gloss enamel paint or applied oil-rubbed bronze.

#### Diffuser

Clear tempered textured glass is .100" thick and slides into housing.

#### **Electrical**

This unit is wired for 120V operation. High/low switch included.


#### Lamping


For use with 20 watt 120V G8 bi-pin xenon lamps included. Lamps are rated for 5,000 hours.

# Certification

Fixtures are cULus listed for damp locations and carry a UL rating for undercabinet mounting.

Specifications and dimensions subject to change without notice.





# **Ordering Information:**

Model No.	Lamps			Dimensi	ons	Mounting	
Finish	120V	Qty	Lamp	Н	W	L	M
White	EXL120WH	1	20W BI-PIN BASE	1-5/16"	4"	9"	5-7/8"
White	EXL220WH	2	20W BI-PIN BASE	1-5/16"	4"	12"	9-1/8"
White	EXL320WH	3	20W BI-PIN BASE	1-5/16"	4"	18"	15-1/8"
White	EXL420WH	4	20W BI-PIN BASE	1-5/16"	4"	24"	21-1/8"
Finish	120V	Qty	Lamp	Н	W	L	M
Oil-Rubbed bronze	EXL120RB	1	20W BI-PIN BASE	1-5/16"	4"	9"	5-7/8"
Oil-Rubbed bronze	EXL220RB	2	20W BI-PIN BASE	1-5/16"	4"	12"	9-1/8"
Oil-Rubbed bronze	EXL320RB	3	20W BI-PIN BASE	1-5/16"	4"	18"	15-1/8"
Oil-Rubbed bronze	EXL420RB	4	20W BI-PIN BASE	1-5/16"	4"	24"	21-1/8"