

Features

- Acrylic
- Pump with air switch and grounding-type plug-in cord
- 8 color-matched Kohler hydro-massage jets
- Integral apron with removable access panel
- Integral lumbar support and armrests to cradle the body
- Left or right drain
- Textured bottom surface
- Three-side integral tile flange for alcove installation
- 60" (1524 mm) x 32" (813 mm) x 20" (508 mm)


Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.7
- UL 1795
- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

BATH WHIRLPOOL WITH INTEGRAL APRON

K-1109-LA
ALSO K-1109-RA



Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Accessories

- CP: Polished Chrome
- PB: Vibrant® Polished Brass
- Other: Refer to Price Book for additional colors/finishes

Specified Model

Model	Description	Colors/Finishes	
K-1109-LA	Bath whirlpool with integral apron – left drain (shown)	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____
K-1109-RA	Bath whirlpool with integral apron – right drain	<input type="checkbox"/> 0	<input type="checkbox"/> Other_____

Recommended Accessories

K-7161-AF	Adjustable pop-up drain	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____
K-7213	Clearflo bath cable drain with PVC tubing	<input type="checkbox"/> CP		<input type="checkbox"/> Other_____
K-7214	Clearflo bath cable drain without PVC tubing	<input type="checkbox"/> CP		<input type="checkbox"/> Other_____

Product Specification

The acrylic bath whirlpool shall be 60" (1524 mm) in length, 32" (813 mm) in width, and 20" (508 mm) in height. Product shall be three-side integral tile flange for alcove installation. Product shall have 8 color-matched Kohler jets and a pump with air switch and grounding-type plug-in cord. Product shall feature integral lumbar support and arm rests. Product shall feature an integral apron with removable access panel and a textured bottom surface. Product shall be available with a left or right drain. Bath whirlpool shall be Kohler Model K-1109-____-____.

PORTRAIT®

Optional Accessories

K-1491	Pillow	<input type="checkbox"/> 0	<input type="checkbox"/> Other _____
K-1601	Footstop	<input type="checkbox"/> 0	<input type="checkbox"/> Other _____

Technical Information

Fixture*:	
Bathing well	
Basin area, bottom	42" (1067 mm) x 20" (508 mm)
Basin area, top	51" (1295 mm) x 24" (610 mm)
Weight	135 lbs (61.2 kg)
To overflow	
Water depth	14" (356 mm)
Capacity	60 gal (227.1 L)
* Approximate measurements for comparison only.	

Pump:	V	Hz	A
1-speed	120	60	7

Required Electrical Service

Dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI):

Pump/control 120 V, 15 A, 60 Hz


Locate the outlet behind the whirlpool and within 24" (610 mm) of the pump.

Installation Notes

Install this product according to the installation guide.

Floor support under whirlpool must provide for a minimum of 50 lbs/square foot (242 kg/square meter) loading.

No change in measurements if connected with drain illustrated. (K-7161-AF)



Product Diagram