


DEVONSHIRE[™] BYPASS BATH AND SHOWER DOORS

K-704410, K-704412, K-704414

FEATURES

- Smooth, cleanable wall jambs
- Frameless 1/4" (6mm) thick tempered safety glass with protected bottom edge for added safety
- Continuous door panel guide mechanism for smooth, quiet sliding action
- Out-of-plumb adjustability allows for easy installation
- Stainless steel hardware prevents fasteners and rollers from rusting or corroding in a damp environment



CODES/STANDARDS

Specified model meets or exceeds the following:

• ANSI Z97.1 (tempered glass)

GLASS OPTIONS

L Crystal Clear

COLORS/FINISHES

- SH Bright Silver Finish
- MX Matte Nickel Finish

SPECIFIED MODEL:


Model	Description	Glass Option Colors/Finishes		
K-704410	Bath and Shower		□SH	□MX
K-704412	Shower		□SH	□MX
K-704414	Shower		□SH	□MX


PRODUCT SPECIFICATION:

Bypass bath and shower door shall have smooth cleanable wall jambs. Door shall have frameless 1/4" (6mm) thick tempered safety glass with protected bottom edge for added safety. Door shall have a continuous door panel guide mechanism for smooth, quiet sliding action. Door shall have stainless steel hardware to prevent rusting on fasteners and rollers. Shower door shall be Kohler Model K-_____-___.

We reserve the right to make revisions without notice in the design of fixtures or in packaging unless this right has specifically been waived at the time the order is accepted.

DEVONSHIRETM





Model	А	B (Max.)	C (Walk Through)
K-704410	58-5/16"	59-5/8"	27-7/8"
	(148.1cm)	(151.4cm)	(70.8cm)
K-704412	70-5/16"	47-5/8"	21-7/8"
	(180.2cm)	(121cm)	(55.6cm)
K-704414	70-5/16"	59-5/8"	27-7/8"
	(180.2cm)	(151.4cm)	(70.2cm)

PRODUCT DIAGRAM

