

Features


- Acrylic
- Integral tile flange
- 60 gallon (227.1 L) capacity
- Arm rests and lumbar support to cradle the body
- Integral apron simplifies alcove installation
- 60" (1524 mm) x 32" (813 mm) x 20" (508 mm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662





Colors/Finishes

- 0: White
- Other: Refer to Price Book for additional colors/finishes

Model	Description	Colors/Finishes				
K-1108-LA	Bath with left drain, integral apron (shown)	0 🗆 0		Other		
K-1108-RA	Bath with right drain, integral apron	0		□ Other		
Recommended Accessories						
K-7160-AF	Drain	□ CP	🗅 PB	Gener		

Specified Model

Product Specification:

The bath shall be 60" (1524 mm) in length, 32" (813 mm) in width, and 20" (508 mm) in height. Bath shall be made of acrylic. Bath shall have integral tile flange, and integral apron. Bath shall have 60 gallon (227.1 L) capacity. Bath shall have lumbar supports and armrests. Bath shall be UL listed. Bath shall Bath shall be Kohler Model K-1108-____.

PORTRAIT_® 5'

Technical Information


Fixture*:	Basin area	Top area	Weight		
Bathing well	42" (1067 mm) x 20" (508 mm)	51″ (1295 mm) x 24″ (610 mm)	80 lbs. (36.3 kg)		
Water depth (to overflow)		Capacity (to overflow)			
14″ (356	mm)	60 gal. (227.1 L)			
* Approximate measurements for comparison only					

Installation Notes

Install this product according to the installation guide.

Floor support under this product must provide for minimum loading of 45 lbs/square foot (222 kg/square meter) loading.

No change in measurements if connected with drain illustrated. (K-7161-AF)



Product Diagram

