# STERLING.

#### Features

- Compression molded from our exclusive solid  $\textit{Vikrell}_{\textit{@}}$  material
- Available with tile or curve wall surrounds
- Durable high-gloss finish
- 10-year consumer/3-year commercial limited warranty
- 60-1/4" (153 cm) x 34" (86.4 cm) x 5-1/2" (14 cm) receptor rough-in dimensions include nailing flange
- 60" (152.4 cm) x 34" (86.4 cm) x 4-1/2" (11.4 cm) unit finished dimensions

# **Codes/Standards Applicable**

Specified model meets or exceeds the following:

- ANSI Z124.1.2
- CSA B45
- ASTM E162
- ASTM E662



MATERIAL STRENGTH. PROVEN PERFORMANCE.



## **Colors/Finishes**

- 0: White
- Other: Refer to Price Book for additional colors/finishes

#### Specified Model

Model	Description	Coloi	rs/Finishes	
72131100	60" (152.4 cm) shower receptor	0 🗆	Other	

# ENSEMBLE

# **Technical Information**

Model	door maximum width	door maximum height	
72131100	*56-5/8" (143.8 cm)	*NA	
* Varies with alternative walls.			


#### **Installation Notes**


Install this product according to the installation guide.

Size the drain cutout to fit the drain assembly that will be used.

Double studding is recommended for pivot shower door installations.

Studs should be positioned roughly as shown.





## **Product Diagram**

