

### Aquatic products may be specified as Lasco Bathware.

# Submittal Sheet

## 521 CMR Compliant\* 1363BFSCMA

CUSTOMER:			JOB NAME:		
PO #:			SHIP TO:		
QUOTE #:		QUANTITY:			
	PLUMBING CONTRACTOR APPROVAL	//		GENERAL CONTRACTOR APPROVAL	/ <sub>DATE</sub> /
	ENGINEER APPROVAL	/		ARCHITECT APPROVAL	//

To complete your order, this document must be signed and faxed to the Aquatic Centralized Customer Service Center.


Fax (866) 544-5353 • Phone (800) 945-2726

IMPORTANT: ADA compliant showers with NO interior threshold will have water escape onto the bathroom floor. Aquatic highly recommends you take the following precautions:

- Install only the minimum number of ADA units without an interior threshold required for each job.
   If possible install Aquatic's accessible models that have a ½ (15) interior threshold to reduce the amount of water that escapes from the shower.
- 2. When installing units with NO interior threshold, install a FLOOR DRAIN to control the water that escapes onto the bathroom floor.
- 3. Depending on your application, you may choose to install Aquatic's vinyl flexible dam or removable threshold, which helps better retain water within the shower. However, these items may not necessarily meet ADA or other code requirements. Always confirm code compliance with your local building authority.

Int. Dim.	36 W x 36 D x 75 H (915 x 915 x 1905)
Ext. Dim.	38 W x 38 ¼ D x 77 H (965 x 970 x 1955)
Skirt Ht.	3/4 (20) skirt, NO interior threshold
Packaged Wt.	182 lbs. (85 kg.) gross
Material	Gelcoat
Warranty	Gelcoat Finished Products — Three Years

inches (mm)



#### STANDARD FEATURES

- Code compliant when fully equipped and installed according to guidelines
- Pre-leveled base
- -Center drain location
- -Slip resistant, textured bottom [ASTM F-462]

#### CONFIGURATION

☐ Fully equipped — 521 CMR*
Includes etched L-shaped grab bar, rectangular fold-up
seat, pressure balancing mixing valve and hand-held
shower assembly per 521 CMR guidelines

#### **ADDITIONAL OPTIONS**

Fixture Wall: Left Right

☐ Etched L-shaped grab bar
□ Etched vertical 18 (455) grab bar
□ Rectangular fold-up seat
☐ Hand-held shower assembly with 36 (915)
slide bar and 60 (1525) hose
□ Pressure balancing mixing valve
□ Soap dish
□ Curtain rod
☐ Shower curtain
Standard Colors: □ Almond □ Biscuit
☐ Bone ☐ Linen ☐ White ☐ Sterling Silver
Other
□ Brass drain
Additional accessories
For pricing of units and additional options, reference the Aquatic Price Book.

\*This configuration may not be compliant in all applications. Call customer service to confirm MA code compliance.

# Submittal Sheet

### Aquatic products may be specified as Lasco Bathware.



All other tolerances: ±1"

## 1363BFSCMA 521 CMR Compliant\*

Please indicate changes needed. FRAMING DIMENSIONS Inches (mm) C D - 15" SLIP-RESISTANT SURFACE 19 19 38 1/8 38 1/4 (970)(480)(970)(480)1 1/2" Installation Options:

1. Install in a recessed pit for rough-in floor installation.

2. Build sub-floor to level finished floor with top of shower skirt. 19 38 1/4" 32 0.A. Ø 31/4" DRAIN 1 1/4" 38" O.A. 1 1/4" 36" INTERIOR 36" INTERIOR 1 1/4" 18" Ø 11/2" ETCHED 10" -HAND HELD L-SHAPED SHOWER **GRAB BAR** WITH SLIDE BAR 77 75" **PRESSURE** BALANCING MIXING 42" VALVE 36" 34 1/2" 18" 3/4" **SECTION A-A** 1/4" RISE/12" **DETAIL B** Shell tolerance: +0, - 3/8" 3/4" SKIRT HEIGHT

FAX TO THE AQUATIC CENTRALIZED CUSTOMER SERVICE CENTER (866) 544-5353