


# HAND SINKS (SE) STANDARD

### **SPLASH MOUNTED FAUCETS**



SINGLE HOLE PUNCH
Faucet omitted

Paucet omitted

Faucet omitted





LARGE SIZE SINK BOWL



Features Large Size Sink Bowl 16" x 20" x 8" 

 Item #: \_\_\_\_\_\_ Qty #: \_\_\_\_\_

 Model #: \_\_\_\_\_\_

 Project #: \_\_\_\_\_\_

Keyhole Bracket for easier installation and greater stability.



#### **FEATURES:**

One piece Deep Drawn sink bowl design.

Sink bowl is 10" x 14" x 5"\*.

(\*7-PS-45 sink bowl size is 16" x 20" x 8")

All sink bowls have a large liberal radii with a minimum dimension of 2" and are rectangular in design for increased capacity.

Keyhole wall mount bracket.

Stainless steel basket drain 1-1/2" IPS.

#### **Specific Features:**

**7-PS-50** features lever operated drain and built-in overflow with plastic overflow tube and spring clamps. P-Trap is 1 1/2".

**7-PS-20** 4" O.C. deck mounted centerset faucet furnished with aerator.

**7-PS-50 & 7-PS-60** 4" O.C. splash mounted gooseneck faucet, chrome plated & furnished with aerator.

**7-PS-45** Same as above plus 2 Support Brackets (Hardware Included).

7-PS-67 features lever operated drain.

**7-PS-68** 4" O.C. splash mounted gooseneck faucet with Wrist Handles, chrome plated & furnished with aerator.

#### **CONSTRUCTION:**

All TIG welded.

Welded areas blended to match adjacent surfaces and to a satin finish. Die formed Countertop Edge with a No-Drip offset.

One sheet of stainless steel - No Seams.

#### **MATERIAL:**

Heavy gauge type 304 series stainless steel.

Wall mounting bracket is Galvanized and of offset design.

All fittings are brass / chrome plated unless otherwise indicated.

#### **MECHANICAL:**

Faucet supply is 1/2" IPS male thread hot and cold.

FOR REPLACEMENT FAUCET, DRAINS AND ACCESSORIES SEE PAGE B-13 & SECTION G



**NEW YORK** 

(800) 645-3166 Fax: (631) 242-6900 **GEORGIA** 

(800) 832-1218 Fax: (770) 775-5625 **TEXAS** 

(800) 527-0353 Fax: (972) 932-4795 **NEVADA** 

(800) 446-8684 Fax: (775) 972-1578

## **DIMENSIONS and SPECIFICATIONS**

TOL Overall: ± .500" Interior: ± .250"

FITTINGS SUPPLIED AS SHOWN

ALL DIMENSIONS ARE TYPICAL

