



## FINISHED AREA ADJUSTABLE CLEANOUT

- Cast iron body comes complete with a nickel, scoriated adjustable head.
- Designed to easily adapt to either cast iron or plastic pipe.

Body Type	Model Number	Dimensions in Inches [mm]					Box Qty.
		Pipe Conn.	A	B	C	D	
No-Hub	CO-2500-NH2	2" [51]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4
	CO-2500-NH3	3" [76]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4
	CO-2500-NH4	4" [102]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4
Push-On	CO-2500-PO2	2" [51]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4
	CO-2500-PO3	3" [76]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4
	CO-2500-PO4	4" [102]	6-1/2" [165]	5" [127]	1/4" [6] Min. 1" [25] Max.	3-3/4" [95]	4

## Options

Suffix	Description
-HD	Heavy-Duty Top
-VP	Vandal Proof