

Features


- Includes SilentShield® sound-absorption technology
- Double (high/low) compartment
- Satin finish
- One-piece steel construction, no center weld
- Includes installation hardware
- Undermount rimless design
- Wide undermount lip
- 19-gauge stainless steel
- Spacious 7" (17.8 cm) and 5" (12.7 cm) deep basin
- 31-3/4" (80.6 cm) x 17-1/2" (44.5 cm) x 7" (17.8 cm)

Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

STAINLESS STEEL HIGH/LOW SINK UCL3322R



Colors/Finishes

- NA: None applicable

Accessories:

- NA: None applicable

Specified Model


Model	Description	Holes	Small Basin Depth	Large Basin Depth	Colors/ Finishes
UCL3322R	Double (high/low) compartment sink	0	5" (12.7 cm)	7" (17.8 cm)	<input type="checkbox"/> NA

Technical Information

Fixture:*		
Sink		
	Small bowl	Large bowl
Basin area	7-1/4" (18.4 cm) x 15-1/4" (38.7 cm)	21" (53.3 cm) x 15-1/4" (38.7 cm)
Water depth	5" (12.7 cm)	7" (17.8 cm)
Drain holes	3-5/8" (9.2 cm) D.	3-5/8" (9.2 cm) D.
* Approximate measurements for comparison only.		
Included components:		
Cut-out template	1030072-7	

Installation Notes

Install this product according to the installation guide.



Product Diagram