



SINGLE CHANNEL WALL MOUNT CONTROLLER

Gas Detection For Life

Beacon™ 110 Model



Features

- Low cost versatile solution
- Compact, weatherproof, NEMA 4X enclosure
- 115/220 VAC or 24 VDC operation
- Long life sensors (2+ years typical)
- Accepts RKI LEL/O₂/CO₂/toxic direct connect sensors
- Accepts any 4-20 mA transmitter
- Audible alarm with reset button
- Two programmable alarm levels
- Built-in trouble alarm with relay
- Relay rating 10 amps, form C
- Provides 4-20 mA output
- Optional Strobe

Industry Applications

- Petrochemical plants
- Refineries
- Water & wastewater treatment plants
- Pulp & paper mills
- Gas, telephone, & electric utilities
- Parking garages
- Manufacturing facilities
- Steel
- Automotive
- HVAC

Gas detection should not be complicated. The Beacon 110 is gas detection simplified.

The Beacon 110 is a powerful, low cost fixed system controller for one point of gas detection. It is microprocessor controlled, simple to install and operate, and priced to be the industry's best value single gas detection controller. It is capable of accepting RKI sensors directly for LEL level combustibles, oxygen, CO₂, and toxic gas sensors. The Beacon 110 can also accept any 4-20 mA transmitter (2 or 3 wire, 24 VDC). Sensors can be mounted directly at the Beacon 110 housing, or can be wired remote from the controller.

The 10 amp rated relay contacts allow direct control of external alarms and horns. The digital display has backlighting and simultaneous readout of the gas type and concentration.

The Beacon 110 is also housed in a NEMA 4X rated case for a weather tight seal. This case design complies with lock out / tag out standards and can be fully secured. An external reset switch allows the alarm to be silenced from outside of the controller housing. The Beacon 110 ships complete with a wall mounting kit for easy installation.

RKI offers the industry's widest selection of standard and toxic gas detection sensors, all of which can be utilized with the Beacon 110, providing gas monitoring protection for almost any application.

RKI Instruments, Inc. • 33248 Central Ave. Union City, CA 94587 • Phone (800) 754-5165 • (510) 441-5656 • Fax (510) 441-5650

World Leader In Gas Detection & Sensor Technology
www.rkiinstruments.com

Beacon™ 110 Model

Physical

Dimensions	Height: 8.5" 216 mm Width: 7.0" 178 mm Depth: 4.3" 109 mm
Enclosure	Wall mounting grey fiberglass with hinged cover
Conduit Connection	3/4" NPT conduit hubs, 2 provided. 1 for sensor wiring and 1 for power & relay wiring
Wiring Termination	Screw type terminal block, 14 gauge max.
Power	Universal 115 VAC & 220 VAC, or 24 VDC nominal, battery backup option available
Controls	3 internal push buttons for setup, programming, and calibration. 1 external push button for alarm reset.

Environmental

Operating Temperature	-4°F to 122°F (-20°C to 50°C)
Storage Temperature	-4°F to 158°F (-20°C to 70°C)
Enclosure Rating	NEMA-4X enclosure, chemical, and weather resistant. Suitable for indoor and outdoor installations.

Inputs

Direct Wired Sensors	LEL, Oxygen, Carbon Dioxide, and toxic gas sensors. Remote amp not required for less than 500 feet
4-20 mA Sensors	Accepts any 4-20 mA transmitter (24 VDC, 2 or 3 wire). A wide variety of RKI/Riken sensors are available with 4-20 mA signals. Wiring distances up to 8,000 feet
Sampling Methods	Diffusion and sample draw heads available

Outputs

Relays	Three relays - 10 amp rating (at 115 VAC), SPDT isolated contacts. 2 relays for gas alarms and 1 trouble relay. Relays fully programmable for: increasing or decreasing alarm, latching or self reset, normally energized or normally de-energized, time delay for alarm on and alarm off.
4-20 mA	Signal output, 4-20 mA (maximum load impedance 500 ohms), per channel
24 VDC	24 VDC (400 mA max) output provided to operate sample drawing adapters or other accessories
Display	2 x 8 Alphanumeric display with backlighting
Audible	Built-in audible alarm, 94 dB, mounted on enclosure Coded output: pulsing = gas alarm, steady = fail
Visual	3 LED's on the front cover for alarm status indication, and malfunction. Optional top-mount strobe

Approvals

Warranty	One year materials and workmanship
-----------------	------------------------------------

Specifications subject to change without notice.

Made in the USA



Toll Free: (800) 754-5165 • Phone: (510) 441-5656
Fax: (510) 441-5650 • www.rkiinstruments.com

Authorized Distributor: