


The Original Since 1981

11750 Roscoe Blvd. Unit 1 Sun Valley, CA 91352

Email: <u>info@falconstainless.com</u> www.falconstainless.com TEL: (818) 767-3569 FAX: (818) 768-8533 Toll Free 1-800-814-8444



Corrugated Stainless Steel Flexible Water Heater/Softener Connectors Specification Sheet

SPECIFICATION:

Furnish and install Corrugated Stainless Steel Water Heater &/or Softener Connectors

DESIGN FEATURES: Mega-flow SUPER Water-flexTM

- 304 Series Stainless Steel
- 3/4" ID SS Flex with 3/4" FIP x 7/8" Copper Sweat
- Sweat Not available in braided type
- Maintains optimum flow no restriction
- Kink and Crimp Free
- Chrome plated brass nut
- Extremely Flexible
- Will not corrode or rust
- No Dielectric union required
- Highest Quality EPDM washer
- Resists work hardening
- Working pressure 200 psi
- Burst pressure approx 1850 psi
- 100% Leak Tested
- Sweat Installation
- Lifetime Warrantee
- Temperature rating 35 250 degrees F
- Bright annealed

COMPLIANCES/LISTINGS:

- * ICC-ES PMG
- * ICC Listed, Tested & Certified
- * UPC, IPC, IMC, IRC (USA)
- * Low Lead Compliant California H & S Code 116875
- * ASME A112.18.6/CSA B125.6-2009 Compliant
- * NSF-61 (ICC-ES PMG Certified to ANSI/NSF section 9)
- * State of Wisconsin, Commonwealth of Massachusetts

		_
Model #	Description	Length
H3404		
SWTxFEMx15	³ / ₄ " FIP x 7/8" Coppe	er Swt 15"
SWTxFEMx18	3/4" FIP x 7/8" Coppe	er Swt 18"
SWTxFEMx24	³ / ₄ " FIP x 7/8" Coppe	er Swt 24"





Date:
Model# Quantity:

