



Corrugated Stainless Steel Flexible Water Heater/Softener Connectors Specification Sheet

SPECIFICATION:

Furnish and install Corrugated Stainless Steel
Water Heater &/or Softener Connectors

DESIGN FEATURES: Mega-flow SUPER Water-flex™

- 304 Series Stainless Steel
- True .72" ID tube
- Flows approx 135% more than braided type
- Maintains optimum flow – no restriction
- Kink and Crimp Free
- Chrome plated brass nuts
- Extremely Flexible
- Will not corrode or rust
- No Dielectric union required
- Highest Quality EPDM washer
- Resists work hardening
- Working pressure 200 psi
- Burst pressure approx 1850 psi
- 100% Leak Tested
- No Sweat Installation
- Lifetime Warrantee
- Temperature rating 40 – 250 degrees F
- Bright annealed

COMPLIANCES/LISTINGS:

- * ICC-ES PMG
- * ICC Listed, Tested & Certified
- * UPC, IPC, IMC, IRC (USA)
- * Low Lead Compliant California H & S Code 116875
- * ASME A112.18.6/CSA B125.6-2009 Compliant
- * NSF-61 (ICC-ES PMG Certified to ANSI/NSF section 9)
- * State of Wisconsin, Commonwealth of Massachusetts

Model #	Description	Length
H3405		
SWC1" x 3/4" x 18"	1" FIP x 3/4" FIP	18"
SWC1" x 3/4" x 24"	1" FIP x 3/4" FIP	24"



ANSI/NSF 61



Compliant to AB1953

ASME A112.18.6

Product Submittal

Job Name: _____

Date: _____

Model# _____ Quantity: _____

Architect/Contractor: _____

