

$\mathsf{SURVIVOR}^{\scriptscriptstyle{\otimes}}$ RIGHT ANGLE, SAFETY-RATED FIREFIGHTER'S FLASHLIGHT







Custom designed optic with optional, interchangeable Smoke-Cutter® plugs for preferred beam pattern:

- · Black plug signifcantly reduces peripheral light for a tighter beam
- Amber plug reduces peripheral light and eye fatigue caused by glare

Material/Lens Housing, base and battery housing made from high impact super tough nylon offering exceptional durability. All openings are O-ring sealed for weather resistance. Spring loaded clip with built in D-ring easily attaches to belts and harnesses and reduces unwanted rotation. One way valve for case venting. Available in international safety orange, high visibility vellow or black

Dims/Weight

Height: 7.06 in. (17.92 cm); Height in charger: 8.67 in. (22.02 cm); Width: 2.85 in. (7.24 cm); Diameter: 2.87 in. (7.29 cm) Grip area: Height: 3.6 in. (9.14 cm);

Thickness: 1.35 in. (3.43cm); Width: 2.20 in. (5.59 cm)

NiMH: 18.0 oz (510 grams) Alkaline: 13.7 oz (388 grams)

Light Source

White LED, impervious to shock with a 50,000 hour lifetime

Custom "Total Internal Reflection" optic for narrow beam and optimum peripheral illumination. Insertable black plug reduces peripheral illumination for improved smoke cutting ability or amber plug reduces eye fatigue.

Output/

Four lighting modes:

· High for a super-bright beam that pierces through smoke: 41,000 candela; 175 lumens; 405m beam distance; runs 3.5 hours (NIMH); runs 4 hours (alkaline) Run time

· Low for bright light and longer run time: 14,000 candela; 60 lumens; 237m beam distance; runs 13 hours (NIMH); runs 15 hours (alkaline)

· Flash for signaling: runs 8 hours

Moonlight mode provides low-level lighting for battery conservation: runs 20 days

Switch Rubber dome push-button actuator provides easy operation even when wearing heavy gloves

Battery Rechargeable NiMH battery also accepts 4 "AA" alkaline batteries

Features

- Reduced bezel length to minimize snag hazards
- · IPX4 water-resistant; 2m impact resistance tested
- · Updated clip design for easy attachment on turnout gear
- Super strong pocket clip

Approvals*

Class I, II, Division 1, Groups C, D, E, F, G; Class III, T-Code: T4

Class I, Division 2, Groups A, B, C, D; T-Code: T4

Flashlight meets 500°F requirements of NFPA 1971-8.6 (2013).

Charger meets requirements of NFPA 1901-14.1.10.2 (2016) mounted in any position.

MSHA: Permissible Flashlight, Approval No. 20-A150001-0.

CEC Compliant (Fast and Smart charger models only)

Warranty

Streamlight warrants this product to be free of defects for a lifetime of use except for batteries and bulbs, abuse and normal wear. We will repair, replace or refund the purchase price of this product should we determine it to be defective. This limited lifetime warranty also excludes rechargeable batteries, chargers, switches and electronics which have a 2 year warranty with proof of purchase. THIS IS THE ONLY WARRANTY, EXPRESSED OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES ARE EXPRESSLY DISCLAIMED EXCEPT WHERE SUCH LIMITATION IS PROHIBITED BY LAW. You may have other specific legal rights which vary by jurisdiction. Visit streamlight.com for full warranty information.

ITEM	UPC	ITEM#
Survivor - 230V AC/12V DC - Yellow	080926-90515-3	90515
Survivor - 230V AC/12V DC - Black	080926-90525-2	90525
Survivor - 230V AC/12V DC - Orange	080926-90505-4	90505
Survivor - 240V AC/12V DC - Yellow	080926-90516-0	90516
Survivor - 240V AC/12V DC - Orange	080926-90506-1	90506
Survivor - 240V AC/12V DC - Black	080926-90526-9	90526
Survivor - 120/100V AC/12V DC Smart Charge - Orange	080926-90503-0	90503
Survivor - 120/100V AC/12V DC Smart Charge - Yellow	080926-90513-9	90513
Survivor - 120/100V AC/12V DC Smart Charge - Black	080926-90523-8	90523

ITEM	UPC	ITEM#
Survivor - 20V/100V AC Fast Charge - Yellow	080926-90512-2	90512
Survivor - 120V/100V AC Fast Charge - Orange	080926-90502-3	90502
Survivor - 120V/100V AC Fast Charge - Black	080926-90522-1	90522
Survivor - 12V DC - Yellow Fast Charge	080926-90519-1	90519
Survivor - 12V DC Fast Charge - Black	080926-90528-3	90528
Survivor - 12V DC Fast Charge - Orange	080926-90509-2	90509
Survivor - (WITHOUT CHARGER) - Yellow	080926-90510-8	90510
Survivor - (WITHOUT CHARGER) - Orange	080926-90500-9	90500
Survivor - (WITHOUT CHARGER) - Black	080926-90520-7	90520
Survivor Alkaline Model - Yellow	080926-90541-2	90541
Survivor Alkaline Model - Orange	080926-90540-5	90540
Survivor Alkaline Model - Black	080926-90545-0	90545

	Item	UPC	Part #
	240V AUS AC Charge Cord	080926-22048-5	22048
	DC2 direct wire charge Cord	080926-22050-8	22050
	DC1 Charge Cord	080926-22051-5	22051
	100V/120V AC Charge Cord	080926-22060-7	22060
	230V AC Charge Cord	080926-22061-4	22061
	240V AC Charge Cord	080926-22062-1	22062
940	Fast Charger/Holder	080926-90118-6	90118
	DC #1 Fast Charger/Holder	080926-90012-7	90012
	DC #2 Fast Charger/Holder	080926-90013-4	90013
	NiMH Battery Pack	080926-90336-4	90336
	Alkaline Battery Carrier (batteries not included)	080926-90542-9	90542