



Hover over image to zoom

# MODEL NO. S806CBL15

Cable Lockout

Adjustable Cable Lockout, 15ft (4.6m) Cable

## BEST USED FOR



Lockout Tagout



Safety Lockout/Tagout



Valve Lockout

## OVERVIEW & FEATURES

### Product Features

- 15ft Cable Lockout
- Patented 5/32in (4mm) diameter x 15ft (4.57m) pull-tight cable adjusts for a secure fit every time. Also available from 7 to 50 feet (2.13m to 15.24m) long
- Integrated safety lockout hasp and cable is ideal for multiple circuit breaker panels and side-by-side gate valve lockouts
- Tough, flexible multi-stranded steel cable is insulated with a clear plastic coating (PVC free)
- Feed the cable end through the points to be locked out, then back through the lockout body
- Cinch it tight to remove any slack with the patented locking feature
- Tough, lightweight thermoplastic body withstands chemicals
- Performs effectively in extreme conditions
- Includes high-visibility, write-on safety labels in English, Spanish and French
- Replaces 8615 Adjustable Cable Lockout Device

### Product Details

The Master Lock No. S806 Adjustable Cable Lockout Device, ideal for group & multi-point lockouts, features a tough, flexible multi-stranded 15ft steel cable insulated with a clear plastic coating. A tough, lightweight Zenex™ Thermoplastic body withstands chemicals and performs effectively in extreme conditions. Includes high-visibility, re-usable write-on safety labels to identify the responsible person & then erase for the next job.

## PRODUCT SPECIFICATIONS

Product Number

S806CBL15

Description

Master Carton Qty	6
Color	Gray