

30 Gallon, 1 Shelf, 2 Doors, Manual Close, Flammable Cabinet, Sure-Grip® EX, Yellow - 893000

Product Images













Short Description

- Designed for the safe storage of chemicals and flammable liquids
- Exterior dimensions of 44 in H x 43 in W x 18 in D (1118 mm H x 1092 mm W x 457 mm D)
- Storage capacity of 30 gal (114 l) of flammable liquids
- Fire-resistant, leak-tested design
- Complies with OSHA, NFPA 30 and NFPA 1
- Fire tested and FM-approved

Description

One of the leading causes of industrial fires is the improper storage and handling of flammable liquids. The Justrite Standard Sure-Grip® EX Flammable Safety Cabinet with Manual Close Doors (model 893000) is designed to safely store flammable liquids. Its exterior dimensions are 44 in H x 43 in W x 18 in D (1118 mm H x 1092 mm W x 457 mm D). These yellow cabinets can store 30 gal (114 l) of flammable liquids.

This model is constructed with a sturdy 18-gauge (1-mm) thick steel double-wall, with 1.5 in (38 mm) of insulating air space for fire resistance. The fully welded, not riveted, construction holds the squareness of the unit for a longer life and offers greater protection in a fire since air gaps are reduced.

High-performance, manual-close, self-latching doors (fail safe, 3-point stainless steel) open to a full 180 degrees and close securely for maximum protection under fire conditions when pushed shut. Continuous piano hinges ensure the doors close smoothly every time.

For added security, each cabinet comes with an innovative U-Loc™ handle that does not require manual rotation to engage the mandatory latch. Cabinets include a cylinder lock and key set, or you can choose to use your own padlock. Trilingual Haz-Alert™ reflective warning labels that read "FLAMMABLE – KEEP FIRE AWAY" are highly visible under fire conditions or during power outages when illuminated with a flashlight.

Model 893000 features one patented, galvanized steel SpillSlope® shelf designed to direct spills to the back and bottom into a 2-in (51-mm) leak-tested sump that meets EPA requirements. Adjustable on 3-in (76-mm)

centers, all SpillSlope shelves meet ANSI MH28.1 standards with a 350-lb (159-kg) safe allowable load. Welded shelf hangers interlock with the shelf to offer maximum stability with no flimsy brackets to lose. For replacement shelves, use models 29943 or 29937.

The cabinet also features dual vents with flame arresters, four adjustable self-leveling feet, and a built-in grounding connector. Its durable lead-free epoxy/polyester powder-coat finish provides excellent chemical resistance inside and out, as well as minimizes the effects of corrosion and humidity.

Justrite supplies more than 300 safety cabinet models ranging from 4- to 115-gal (15- to 435-l), to meet a versatile range of safety, compliance, and storage requirements.

All Justrite cabinets carry a 10-year warranty. Model 893000 is tested and approved by FM Approvals. It complies with OSHA, NFPA 30, and NFPA 1 requirements.

Safety Considerations for Standard Safety Cabinets

The requirements for handling and storing chemicals are complex and depend on how flammable the liquid is. There is no room for error, so it is critical to choose a safety cabinet that has been independently tested to meet the standards of your industry and local jurisdictions. Not just any safety cabinet will do. Justrite flammable cabinets are best in class and are trusted within a wide range of industrial settings across the world, including laboratories, manufacturing, oil refineries, chemical processing plants and more.

For more information, please consult our workplace safety article about the requirements for flammable liquid storage.

Specifications

Model No	893000
UPC	697841110892
International Model No.	8930001
Color	Yellow
Pallet Quantity	2
Material Specifications	18-Gauge Steel
FM Approval	Yes
OSHA Compliance	Yes
Complies with NFPA Code 30	Yes
Capacity	30 gallon
Liter Capacity	114
Number of Doors	2
Number of Doors	2
Door Type	Manual
Door Type	Manual
Door Type Number of Shelves	Manual 1
Door Type Number of Shelves Adjustable Shelves	Manual 1 Yes
Door Type Number of Shelves Adjustable Shelves	Manual 1 Yes 44" H x 43" W x 18" D
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D 39.6" H x 39.5" W x 14.6" D
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior Dimensions, Interior	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D 39.6" H x 39.5" W x 14.6" D 1006mm H x 1003mm W x 370mm D
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior Dimensions, Interior Height (Inches)	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D 39.6" H x 39.5" W x 14.6" D 1006mm H x 1003mm W x 370mm D 44
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior Dimensions, Interior Height (Inches) Width (Inches)	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D 39.6" H x 39.5" W x 14.6" D 1006mm H x 1003mm W x 370mm D 44 43
Door Type Number of Shelves Adjustable Shelves Dimensions, Exterior Dimensions, Interior Height (Inches) Width (Inches) Depth	Manual 1 Yes 44" H x 43" W x 18" D 1118mm H x 1092mm W x 457mm D 39.6" H x 39.5" W x 14.6" D 1006mm H x 1003mm W x 370mm D 44 43 18