


6' Length, 2 Channel Speed Bump-Cable Protector, Yellow - 1792

Product Images



Short Description

- 6' Speed Bump & Cable Protector adds safety to your facility
- Constructed of high-visibility yellow high density polyethylene
- Inside Channel Dimensions are 1.25"w x 0.875"h (3.2 x 2.3 cm)

Description

6' Speed Bump Cable Protector adds safety to your facility. Constructed of high-visibility yellow high density polyethylene (HDPE) this bump is engineered at the perfect angle. Also acts as a dual channel cable protector, feature a non-skid surface, and is weather and chemical resistant. HDPE construction means you eliminate the need to continually paint bumps. Load limit of 20,000 lbs. per Pneumatic Tire. Anchor kit included with six 1/2"d x 14"l spikes and one tube of asphalt adhesive). Inside Channel Dimensions are 1.25"w x 0.875"h.

Specifications

Model No	1792
Color	Yellow
Dimensions, Exterior	10W x 72D x 2H
UPC	048441001248
Material Specifications	High-Density-Polyethylene
Pallet Quantity	51
Net Weight, lbs	20
Net Weight, kgs	9.07