


TWIST-ON CONNECTORS

APPLICATION

Twist-on Connectors are designed for direct bury applications and are used to splice and connect multiple wires for continued conductivity. Prefilled with dielectric silicone sealant to protect wires from corrosion.


SPECIFICATIONS

SCB-01 / SCB-01-BLK



A - 2.00" B - 0.81" C - 0.62"

SCB-01-LG



A - 2.41" B - 0.99" C - 0.78"

Max voltage: 600V Size: 2" x 13/16" Wire Type: copper-clad steel; solid and stranded copper Wire Range: min 22-AWG / max 8-AWG Temperature Rating: 105°C (221°F) Sealant Temp: -45°F to 400°F Max 4 – 12-AWG wires

Max voltage: 600V Size: 2 13/32" x 63/64" Wire Type: copper-clad steel; solid and stranded copper Wire Range: min 14-AWG / max 6-AWG Temperature Rating: 105°C (221°F) Sealant Temp: -45°F to 400°F Max 6 – 12-AWG wires

INSTALLATION INSTRUCTIONS

- 1. Strip wires 5/8" for SCB-01 or $\frac{3}{4}$ " for SCB-01-LG
- 2. Align conductors
- 3. Pre-twisting unnecessary; Place stripped wires together with ends of insulation even
- 4. Push wires firmly into connector
- 5. Twist connector onto wires pushing firmly until tight; do not overtighten
- 6. Wipe sealant in and around conductors and connector opening while tightening

Do not reuse.

SCB-01

Twist-on Connector – Regular qty. 20

SCB-01-BLK Twist-on Connector –

Regular qty. 100



SCB-01-LG Twist-on Connector – Large qty. 8



Color: blue only

FEATURES AND BENEFITS

- Designed for direct bury
- Pre-filled dielectric silicone sealant protects wire and never hardens
- Waterproof, corrosion resistant
- Easy installation

