

ANALYSIS

PROCEDURE

1.	Fill Water Sample Collecting Bottle [0688] with sample water.
2.	Press and hold  until colorimeter turns on.
3.	Press  to select Testing Menu .
4.	Scroll to and select 045 Fluoride from menu.
5.	This test requires a reagent blank. Rinse a clean colorimeter tube [0290] and fill to the 10 mL with clear, colorless, Fluoride free water.
6.	Use the 0.5 mL pipet [0353] to add 0.5 mL of *Sodium Arsenite Solution [4128]. Cap and mix.
7.	Use the 1.0 mL pipet [0354] to add 2 measures of *Acid-Zirconyl SPADNS Reagent [3875]. Cap and mix thoroughly. [This is the reagent blank.] Dry the tube with a lint-free cloth.
8.	Insert tube. Close lid. Select Scan Blank .
9.	Rinse tube [0290] three times with the standard. Fill the tube to the 10 mL line. Cap tube. Dry tube.
10.	Use the 0.5 mL pipet [0353] to add 0.5 mL of *Sodium Arsenite Solution [4128]. Cap and mix.
11.	Use the 1.0 mL pipet [0354] to add 2 measures of *Acid-Zirconyl SPADNS Reagent [3875]. Cap and mix thoroughly. [This is the reagent blank.] Dry the tube with a lint-free cloth.
12.	Insert tube. Close lid. Select Scan Sample . Record result as FLUORIDE .

*Reagent is a potential health hazard.

READ SDS: lamotte.com.

Emergency information:

Chem-Tel USA 1-800-255-3924

Int'l, call collect, 813-248-0585



CALIBRATION

Standards

Calibrate meter with fluoride standards. Use a distilled or deionized water blank and one fluoride standard of known concentration.

PROCEDURE

1.	Press and hold  until colorimeter turns on.
2.	Press  to select Testing Menu .
3.	Scroll to and select 045 Fluoride from menu.
4.	This test requires a reagent blank. Rinse a clean colorimeter tube [0290] and fill to the 10 mL with clear, colorless, Fluoride free water.
5.	Use the 0.5 mL pipet [0353] to add 0.5 mL of *Sodium Arsenite Solution [4128]. Cap and mix.
6.	Use the 1.0 mL pipet [0354] to add 2 measures of *Acid-Zirconyl SPADNS Reagent [3875]. Cap and mix thoroughly. [This is the reagent blank.] Dry the tube with a lint-free cloth.
7.	Insert tube. Close lid. Select Scan Blank .
8.	Rinse tube [0290] three times with the standard. Fill the tube to the 10 mL line. Cap tube. Dry tube.
9.	Use the 0.5 mL pipet [0353] to add 0.5 mL of *Sodium Arsenite Solution [4128]. Cap and mix.
10.	Use the 1.0 mL pipet [0354] to add 2 measures of *Acid-Zirconyl SPADNS Reagent [3875]. Cap and mix thoroughly. [This is the reagent blank.] Dry the tube with a lint-free cloth.
11.	Insert tube. Close lid. Select Scan Sample .
12.	Press  or  to scroll to the concentration of the standard.
13.	Press  to save the value. Press  and  at any time to return to the default value.

For additional information see the DC1500 Fluoride manual.

NOTE: Use the AC wall adapter to rapidly charge the meter.

Reinsert the USB port plug after charging.

WARNING: Only use the USB cable [1720-01] that is supplied with the kit. Make no substitutions.



802 Washington Ave · Chestertown · Maryland · 21620 · USA
+1 410-778-3100 · 800-344-3100 · lamotte.com