

2 1/2" NH (65 mm) Hydrant Flow Test Kit, With Case

STYLE AHTK-25NST-16-LG

- Includes a 2 1/2" NH barrel with a pitot tube positioned in the waterway and water diffuser assembly
- 3 1/2" liquid filled 0-160 psi (0-1100 kpa) gauge
- Supplied with flow charts for accurate measuring

Former style: HK-25

No Special Thread

Features

- Includes a 2 1/2" NH barrel with a pitot tube positioned in the waterway and water diffuser assembly
- 3 1/2" liquid filled 0-160 psi (0-1100 kpa) gauge
- Supplied with flow charts for accurate measuring
- Pitot tube is positioned for accurate readings
- Black case

No Special Thread



Specifications

Style	AHTK-25NST-16-LG
Type	Hydrant Test Kit
Swivel Inlet	2.5" (63.5mm)