



**KODIAK
CONTROLS®
INC.**


Master Distributor of Instrumentation,
Controls, and Engineered Solutions for
Industrial and OEM Applications

KODIAK KC102 SERIES PRESSURE GAUGE

Kodiak's 100 series pressure gauges are an inexpensive utility gauge for commercial and industrial applications. This series gauge is commonly used on air, water, oil, or gas applications that are compatible with brass/bronze and on applications without excessive vibration or pulsations.

Specifications

Dial Sizes:	1.5", 2", 2.5", 3.5"
Case:	Black Painted Steel
Wetted Parts:	Brass/Bronze
Bezel:	Crimped with Chrome Plating
Lens:	Polycarbonate
Pointer:	Black Aluminum
Connection:	Center Back Mount 1.5" Dial - 1/8" NPT 2" Dial - 1/8" or 1/4" NPT 2.5" Dial - 1/4" NPT 3.5" Dial - 1/4" NPT
Scale:	Standard: PSI/BAR (x100 = kPa)
Accuracy:	3-2-3%
Dry Non-Fillable Temperature:	-40°F/160°F



	Unit	A	B	C	D
1.5" Dial	IN	1.64	0.93	0.63	1.56
	MM	42	24	16	39
2" Dial	IN	2.07	1.03	0.83	1.86
	MM	53	26	21	47
2.5" Dial	IN	2.50	1.17	0.86	2.03
	MM	63	30	22	52
3.5" Dial	IN	3.97	1.19	0.83	2.02
	MM	114	34	21	55



Options*

- Custom Dials
- Special Connection Threads (BSP, SAE, etc.)
- Glass Lens
- NIST Certificates of Calibration

*Lead times and minimum orders may apply

Example:

KC102 15 8 160

Dial Size:

15 = 1.5"
20 = 2"
25 = 2.5"
35 = 3.5"

Thread Size:

8 = 1/8" NPT
Blank = 1/4" NPT

Ranges:

15 psi 10000 psi
30 psi 30" Hg Vac
60 psi 30" Hg/15 psi
100 psi 30" Hg/30 psi
160 psi 30" Hg/60 psi
200 psi 30" Hg/100 psi
300 psi 30" Hg/150 psi
400 psi 30" Hg/300 psi
600 psi