


FEATURES

- 12" rough-in
- Elongated bowl
- Combination toilet
- Vitreous china
- 10-1/4" x 9-1/8" water area
- 2" glazed trapway
- Includes seat and cover
- Includes lift knob
- Less supply
- 1.6 gpf
- With Insuliner® insulated tank lining (-U)



CODES/STANDARDS APPLICABLE

Specified model meets or exceeds the following:

- ASME/ANSI A112.19.2M
- ASME/ANSI A112.19.6M
- Energy Policy Act of 1992 (EPACT)

COLORS/FINISHES

- 0 White
- Other Refer to Fixtures Price Book for additional colors

Accessories:

- CP Polished Chrome
- Other Refer to Price Book for additional colors

SPECIFIED MODEL:

Model	Description	Colors/Finishes	
K-3463	Elongated bowl toilet	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other_____
K-3463-U	Elongated bowl toilet with insuliner	<input type="checkbox"/> 0 White	<input type="checkbox"/> Other_____

Recommended Accessories				
K-7637	3/8" angle supply with stop	<input type="checkbox"/> CP	<input type="checkbox"/> PB	<input type="checkbox"/> Other_____

PRODUCT SPECIFICATION:

The elongated toilet combination shall be 12" rough-in. Toilet shall be made of vitreous china. Toilet shall have 10-1/4" x 9-1/8" water area. Toilet shall have 2" glazed trapway. Toilet shall include seat and cover. Toilet shall include lift knob. Toilet shall be less supply. Toilet shall be 1.6 gpf. Toilet shall have Insuliner® insulated tank lining (-U). Toilet shall be Kohler Model K-3463-_____-_____.

