ForceFlex Goggle

Specification Sheet

PRODUCT DESCRIPTION:

We rewrote book on how a goggle should look, fit, perform and flex. The ForceFlex[®] soft shell goggle surpasses ANSI Z87+ standards. Its full TPR body forms a tight seal to protect from small particles, debris, liquids, and injury. ForceFlex[®] is the new standard for light weight, low profile, comfortable goggles.

FEATURES:

- The Most Flexible Goggle on the Planet
- Durable, ultra-flexible multi-polymer frame for all day comfort
- Perfect seal protects from small particles and debris
- Elastic head band for the perfect fit
- 3 point ratcheting temples

TECHNICAL DATA FOR: FFG110AF

Frame Material: TPR Lens Design: Dual Dielectric: Yes Strap: Elastic



Packaging: Multicolor Gravity Feed Case Pack: 144 PR per CS Case Dimensions: 26.772 x 12.992 x 14.567 IN Case Weight: 22.000 LB Meets or exceeds the following certifications: ANSI Z87+ Country of Origin: Taiwan

Item No:	Lens Options:	<u>VLT %:</u>	Frame Color:	Vent:	Strap:
FFG110AF	Clear, Anti-fog	85	Gray	Indirect Vented	Elastic
FFG112AF	Gray, Anti-fog	12	Gray	Indirect Vented	Elastic

MCR Safety • 5321 E. Shelby Drive • Memphis, TN • 38118 • USA Phone: 901-795-5810 • Toll Free: 800-955-6887 • Fax: 800-999-3908 • www.mcrsafety.com

©2012 MCR Safety - All Rights Reserved