




AVALANCHE™ ErgoHeight™ 17" High Elongated Toilet

12" Rough-in

Features:

- 1.6 gpf (6.0 Lpf)
- ADA Elongated Bowl
- Elegant Slimline Tank With Side Trip Lever (Right Hand Tank Lever Optional)
- Fluidmaster® Fill Valve
- Gerber XP3 Flushing Technology
- 3" Flush Valve
- Glazed Trapway
- Reverse Trap
- Dual Feed Jet
- White, Bone and Biscuit
- Color-Matched Tank Lever
- 2 Bolt Caps
- Optional insulated tank to minimize condensation (use tank #28-892)



Specifications: Bowl—#21-828 Elongated Bowl
Seat not included
7

Tank-#28-890

Dimensions:

Height30 1/2"
Width17 1/2"
Depth28 7/8"
Rough-in12"
Water Surface from Rim5 $1/4$ "
Trapway (min)2"
Water Surface10" x 8 $1/2$ "
Water Seal2 1/2"
Shipping Weight86 lbs

28⁷/₈"

30¹/₂"

17¹/₂"

16¹/₂"

THIS FIXTURE QUALIFIES
ACCORDING TO ASME TEST
PROCEDURES AS A LOW
CONSUMPTION WATER CLOSET
WITH AN AVERAGE CONSUMPTION
OF 1.6 gpf (6 Lpf) OR LESS.






www.gerberonline.com

Job Name	
Date	
Model Specified	
Quantity	
Customer	
Contractor	
Architect/engineer	



21-818

17" High Elongated, 12" Rough-in (Bowl 21-828 with Tank 28-890)



NOTES:

All dimensions are in inches.

Illustrations may not be drawn to scale.

IMPORTANT:

Dimensions of fixtures are nominal and may vary within the range of tolerances established by ASME Standard A 112.19.2.

THIS FIXTURE QUALIFIES ACCORDING TO ASME TEST PROCEDURES AS A WATER CLOSET WITH AN AVERAGE CONSUMPTION OF 1.6 gpf (6 Lpf) OR LESS.

VITREOUS CHINA