# 15.1 Replacement Parts

# A4/M4 Replacement Parts

Pun	np Head Components	Part No.	QTY Req'd	
1	Spacer	2		
2	Complete Roller Assembly		1	
	NL / NP	A4-MNL-R		
	TH / TK / TKK / THH	A4-MTH-R		
	NH / NK / NHH / NHL / NHHL	A4-MNH-R		
	NKL / NKKL	A4-MNKL-R		
	GH / GK / GKK	A4-MGH-R		
3	Tubing (Reference Tubing Matrix)		1	
4	Pump Head Cover	A4-SXX-C	1	
5	Thumb Screws	90011-183	8	
6	Shaft Extension	90007-128	1	
Pol	lor Assambly Parts	Part No	OTV Pag'd	

Rol	er Assembly Parts	Part No.	QTY Req'd		
7	A4 ROTOR BODY	76010-042*	1		
8	SPIDER RING	76002-038*	1		
9	10-32 CAPTIVE SCREW	90011-341*	2		
	A4 ROTOR ASSY (7,8, and 9)	71010-799	799 1		
10	ARM ROLLER GUIDE	71010-771	2		
11	ARM ROLLER				
	NL / NP	71010-766	2		
	TH / TK / TKL / THH	71010-767	2		
	NH / NK / NHH / NHL / NHHL	71010-768	2		
	NKL / NKKL	71010-769	2		
	GH / GHH / GK /GKK	71010-770	2		

\*Only available as part of Rotor Assy 71010-799

Qui	ck Disconnect Fittings*	Part No.	QTY Req'd
12	Quick Disconnect Fittings		1
	.50" M/NPT FKM	KIT-QMV	
	.50" M/NPT EP	KIT-QME	
	.50" M/NPT Aflas	KIT-QMA	
	.50" Barb FKM	KIT-QBV	
	.50" Barb EP	KIT-QBE	
	.50" Barb Aflas	KIT-QBA	


<sup>\*</sup>For use only with "Q" style pump tubes

Mis	cellaneous Parts*	Part No.	QTY Req'd
Α	Stainless Steel Mounting Bracket	72000-379	1
В	Stainless Steel Mounting Bracket (Extended)	72000-380	1
С	Rubber Feet	90003-561	1


<sup>\*</sup>Sold Separately







\*Pump Head not for sale. For more information please contact a local sales representative.





### **FLEXFLO® Model Number**

М	1/2" N	/2" Male NPT Fitting, Natural PVDF (Kynar)			
В	1/2" [[	D Tubing Barb Fitting, Natural PVDF (Kynar	)		
Q		k Disconnect, Natural PVDF (Kynar). NP flow rate reduced 16.5% with Quick Disconnect connections yes sold separately)			
С	1/2" -	3/4" Tri-clamp connections, Natural PVDF (	Kynar)		
МВ	1/2" N	lale BSPT Fitting, Natural PVDF (Kynar)			
	Pump	o Tube Material, Pump Tube Siz	е		
	GH	Flex-A-Thane® .312 ID	NHHL	Flex-A-Prene® .250 ID (Dual Tube)	
	GHH	Flex-A-Thane® .312 ID (Dual Tube)	NNKK	Flex-A-Prene® .375 ID	
	GК	Flex-A-Thane® .375 ID	NL	Flex-A-Prene® .500 ID	
	GKK	Flex-A-Thane® .375 ID (Dual Tube)	NP	Flex-A-Prene® .750 ID	
	NH	Flex-A-Prene® .250 ID	TH	Flex-A-Chem® .250 ID	
	NHL	Flex-A-Prene® .250 ID	TK	Flex-A-Chem <sup>®</sup> .375 ID	
	NHH	Flex-A-Prene® .250 ID (Dual Tube)	TKK	Flex-A-Chem <sup>®</sup> .375 ID (Dual Tube)	

# **Output Specifications**

Tube Material / Size =	Feed Rate			Max Speed	Max Pressure	Max Temperature
Materiai / Size =	GPH LPH		mL/Min	RPM	PSI (bar)	°F (°C)
lex-A-Thane® Tube						
GH	Up to 39.6	Up to 150	Up to 2500	125	65 (4.5)	130 (54)
GHH	Up to 71.0	Up to 268	Up to 4479	125	65 (4.5)	130 (54)
GK	Up to 55.5	Up to 210	Up to 3500	125	65 (4.5)	130 (54)
GKK	Up to 100	Up to 378	Up to 6300	125	65 (4.5)	130 (54)
lex-A-Prene® Tube						
NH	Up to 28.5	Up to 108	Up to 1800	125	125 (8.6)	185 (85)
NHL	Up to 28.5	Up to 108	Up to 1800	125	65 (4.5)	185 (85)
NHH	Up to 54.0	Up to 204	Up to 3400	125	100 (6.9)	185 (85)
NHHL	Up to 54.0	Up to 204	Up to 3400	125	65 (4.5)	185 (85)
NK	Up to 50.7	Up to 192	Up to 3200	125	80 (5.5)	185 (85)
NL	Up to 100	Up to 378	Up to 6300	125	50 (3.4)	185 (85)
NP	Up to 158.5	Up to 600	Up to 10000	125	30 (2.1)	185 (85)
lex-A-Chem® Tube						
TH	Up to 25.4	Up to 96	Up to 1603	125	30 (2.1)	130 (54)
TK	Up to 54.0	Up to 204	Up to 3400	125	30 (2.1)	130 (54)
TKK	Up to 126	Up to 477	Up to 8000	125	30 (2.1)	130 (54)

<sup>\*\*</sup> NP flow rate reduced 16.5% with Quick Disconnect connections.

#### 16.0 ACCESSORIES

The following accessories are available for the A4 FLEXFLO® Peristaltic Metering Pump. Please visit Bluewhite.com for more information. All accessories are sold separately.



\*KIT-M12-3 for 3 Cables \*KIT-M12-6 for 6 Cables

#### KIT-M12

Kit contains: Two M12 cables. 10 foot length.

KIT-M12-2-15 15 foot length. KIT-M12-2-30 30 foot length.

KIT-M12 WIRING INSTRUCTIONS					
DIAGRAM	PIN#	WIRE COLOR			
	PIN 1	BROWN			
P2 P1	PIN 2	WHITE			
. ( P5	PIN 3	BLUE			
P3 P4	PIN 4	BLACK			
	PIN 5	GRAY			

NOTE: THIS DIAGRAM IS FOR THE PUMP'S M12 PORT



#### **CABLE-UAC**

Kit contains: One 3' USB-A to USB-C cable.



#### KIT-DP3

Kit contains: One 3' profibus cable.



\*KIT-QME for EP O-rings

## KIT-QMV

Kit contains: One Quick Connect Inlet with .50"M/NPT (assembled with FKM O-rings) and One Quick Connect Outlet with .50"M/NPT (assembled with FKM O-rings)



\*KIT-QBE for EP O-rings

## KIT-QBV

Kit contains: One Quick Connect Inlet with .50" hose barb connection (assembled with FKM O-rings), One Quick Connect Inlet with .50" hose barb connection (assembled with FKM O-rings) and two #5 Clamps.



#### **KIT-PSM**

Kit contains: One HDPE Bracket, (4) 3/8" x 2-3/4" long dia anchor bolts.



#### **POWER CORDS - DETACHABLE**

90010-663 115V/60Hz NEMA 5/15 90010-664 220V/50Hz CEE 7/V11 90010-665 230V/50Hz BS 1363/A 90010-666 240V/50Hz AS 3112 90010-696 230V/60Hz NEMA 6/15 90010-711 115V/60Hz NEMA 5/15 (Lockable)