

KITCHEN SINK FAUCET K-15251


Features

- Metal construction
- Reversible quarter-turn washerless ceramic disc valves
- For 8" (20.3 cm) centers
- 7-5/8" (19.4 cm) swing spout reach
- Available with sculptured acrylic, blade, or lever handles
- Lower flow aerator options available (refer to the Kohler Price Book)
- 2.2 gallons (8.3 L) per minute maximum flow rate

Codes/Standards Applicable

Specified model meets or exceeds the following at date of manufacture:





- ADA
- ASME A112.18.1/CSA B125.1
- ICC/ANSI A117.1
- Energy Policy Act of 1992
- NSF 61
- All applicable US Federal and State material regulations



Colors/Finishes

- CP: Polished Chrome

Specified Model

| Model | Description | Sculptured Acrylic  | Blade  ADA | Lever  ADA |
|----------------------|--|---|--|--|
| K-15251 | Kitchen sink faucet | <input type="checkbox"/> CP | | |
| K-15251-B | Kitchen sink faucet | | <input type="checkbox"/> CP | |
| K-15251-4 | Kitchen sink faucet | | | <input type="checkbox"/> CP |
| Optional Accessories | |  | | |
| K-15280 | 12" (30.5 cm) swing spout with aerator | <input type="checkbox"/> CP | | |


Product Specification

The two-handle kitchen sink faucet shall be of metal construction. Product shall have a maximum flow rate of 2.2 gallons (8.3 L) per minute with lower flow aerator options available (refer to the Kohler Price Book). Product shall feature reversible quarter-turn washerless ceramic disc valves and a 7-5/8" (19.4 cm) swing spout reach. Faucet shall be for 8" (20.3 cm) centers. Product shall be available with sculptured acrylic, blade, or lever handles. Faucet shall be Kohler Model K-15251-____-CP.

CORALAIS®

Installation Notes

Install this product according to the installation guide.



Product Diagram