

### KITCHEN SINK FAUCET K-P15172 PROJECT PACK

#### FEATURES

- Metal construction
- One-piece self-contained ceramic disc valve allows both volume and temperature control
- Temperature memory allowing faucet to be turned on and off at any temperature setting
- High-temperature limit stop
- Available with an 8-1/2" (21.6cm), 10" (25.4cm), or 12" (30.5cm) swing spout
- 2.2 gallons (8.3L) per minute
- Lever handle
- Handspray
- 22" (55.9cm) long stainless steel flexible hose connections
- Packaged six per case

#### CODES/STANDARDS APPLICABLE


Specified model meets or exceeds the following:

- ASME/ANSI A112.18.1M
- CSA International B125
- Energy Policy Act of 1992
- IAPMO/UPC
- NSF 61

#### SPECIFIED MODEL:

Model	Description	
K-P15172-F	With 8-1/2" (21.6cm) Swing Spout	<input type="checkbox"/> CP
K-P15172-FL	With 10" (25.4cm) Swing Spout	<input type="checkbox"/> CP
NOTE: All faucets, come with black handspray and matching finish trim ring.		

Optional Accessory		
K-15179-A	12" (30.5cm) Swing Spout and Aerator	<input type="checkbox"/> CP




#### COLORS/FINISHES

- CP Polished Chrome

#### PRODUCT SPECIFICATION:

Single-control kitchen sink faucet shall be of metal construction. The valve shall be a one-piece, self-contained ceramic disc valve, and allows both volume and temperature control. The valve shall feature temperature memory, allowing the faucet to be turned on and off at any temperature setting, and includes a high-temperature limit stop. Product shall include 8-1/2" (21.6cm), 10" (25.4cm), or 12" (30.5cm) swing spout, lever handle, and handspray. Product shall include 22" (55.9cm) long stainless steel flexible hose connections. Faucet shall be Kohler Model K-P15172-\_\_\_\_-CP. Project Pack faucets are packaged six per case.



A	B	C
8-1/2" (21.6cm)	5-1/8" (13cm)	6-1/4" (15.9cm)
10" (25.4cm)	6-1/4" (15.9cm)	7-1/4" (18.4cm)

PRODUCT DIAGRAM