

K-45 & K-45AF Drain Cleaning Machines

K-45/K-45AF



K45-Drain-Cleaning-Machine The K-45 family of drain guns are the professional's choice for cleaning small secondary drain lines from 3/4" to 2 1/2". Available in manual and AUTOFEED versions, each provide you with:

- **Variable Speed Operation** – Fully variable from 0-600 RPM to give you complete control in every situation.
- **Leak Proof** – Inner drum prevents leakage to keep job site clean.
- **Other Features**
 - Quick acting slide chuck to lock cable.
 - Inner drum design virtually eliminates cable flip-over and allows for quick cable change out.
 - Premium quality, compression wound inner core cable combines strength and flexibility to resist kinking.

K-45AF – AUTOFEED

The Advanced 2-Way AUTOFEED lets you clean drains better and faster than ever before – keeps hands off cable and gives you total control to completely work through blockages and retrieve obstructions.

- **Reduce Job Time by 15%** – Advance and retrieve cable without stopping to reverse the motor.
- **Better Results** – Quickly work back and forth through the blockage to completely clear the line.

Specifications

Motor Rating: 120V, single phase, AC, 3.2 amp, 50/60 Hz.

Operating Speed: 0-600 RPM

Drain Line Capacity: 3/4" – 2 1/2"

Drum Capacity: 50' of 5/16"
35' of 3/8"

Weight w/C-1IC 12.6 lbs (K-45)

Cable: 13.8 lbs (K-45AF)