








































SPECIFICATIONS

TPI	LENGTH X WIDTH X THICKNESS		1-PACK PROD NO	5-PACK PROD NO	25-PACK PROD NO	50-PACK PROD NO	APPLICATION
	IN	MM					
4	6 x 3/4 x .050	152 x 19 x 1.3	20574S634R	20575634R	—	—	
6	4 x 3/4 x .050	102 x 19 x 1.3	—	20449456RP	—	—	
6	6 x 3/4 x .050	152 x 19 x 1.3	20571S636RP	20570636RP	20497B636RP	—	
6	6 x 3/4 x .035	152 x 19 x .9	20559S606R	20560606R	20492B606R	—	 
6	6 x 7/16 x .050	152 x 11 x 1.3	20557S676RC	20556676RC	—	—	 
6	6 x 3/4 x .050	152 x 19 x 1.3	20573S656R	20572656R	20530B656R	22750OSB656R	
6	9 x 3/4 x .050	229 x 19 x 1.3	20587S956R	20582956R	20558B956R	22752OSB956R	
6	12 x 3/4 x .050	305 x 19 x 1.3	20586S156R	20585156R	20495B156R	22755OSB156R	
10	6 x 3/4 x .035	152 x 19 x .9	20561S610R	20562610R	20493B610R	22761OSB610R	
10	8 x 3/4 x .050	203 x 19 x 1.3	20581S810R	20580810R	20590B810R	22753OSB810R	  
10/14	6 x 3/4 x .050	152 x 19 x 1.3	20592660R*	20374650R5	20515B650R	—	
10/14	8 x 3/4 x .050	203 x 19 x 1.3	—	20577850R	20535B850R	—	  
10/14	12 x 3/4 x .050	305 x 19 x 1.3	20584S110R	20583110R	20491B110R	22758OSB110R	
10/14	6 x 3/4 x .035	152 x 19 x .9	—	12129635R	—	—	
10/14	8 x 3/4 x .035	203 x 19 x .9	—	12130835R	—	—	 
14	3-5/8 x 5/16 x .035	92 x 8 x .9	—	20520314RC	—	—	  
14	4 x 3/4 x .035	102 x 19 x .9	20551S414R	20550414R	20488B414R	22760OSB414R	
14	6 x 3/4 x .035	152 x 19 x .9	20565S614R	20564614R	20494B614R	22756OSB614R	 
14	8 x 3/4 x .035	203 x 19 x .9	—	21519814R	—	—	
18	3-5/8 x 5/16 x .035	92 x 8 x .9	20522S318RC	20521318RC	—	—	 
18	4 x 3/4 x .035	102 x 19 x .9	20553S418R	20552418R	20489B418R	22759OSB418R	
18	6 x 3/4 x .035	152 x 19 x .9	20567S618R	20566618R	20529B618R	22751OSB618R	 
18	8 x 3/4 x .035	203 x 19 x .9	20563S818R	20578818R	20487B818R	22754OSB818R	 
18	12 x 3/4 x .035	305 x 19 x .9	—	21510118R	21511B118R	—	
24	4 x 3/4 x .035	102 x 19 x .9	20555S424R	20554424R	20490B424R	—	
24	6 x 3/4 x .035	152 x 19 x .9	20569S624R	20568624R	20496B624R	22757OSB624R	
24	8 x 3/4 x .035	203 x 19 x .9	—	20579824R	—	—	