

Residential Upright Energy Saver Electric Water Heater



Photo is of
M-2-50T6DS



Copper Screw Type Immersion Element
(Incoloy type immersion element available upon request)

The Upright Electric Models Feature:

- **DOE**—All residential storage models meet or exceed efficiency requirements of the Department of Energy, ASHRAE Standard 90.1 b (current standard) and the National Appliance Energy Conservation Act of 1987 recent amendment effective January 20, 2004 which supercedes all state and local efficiency requirements.
- **Fully Automatic Controls**—Fast acting surface-mount thermostats for automatic temperature control. Factory installed sensitive manual reset energy cutoff for safety to prevent overheating.
- **Direct Heat Transfer With Immersed Elements**—Transfers heat directly and efficiently to the water. Screw-in style.
- **Factory Installed Hydrojet[®] Total Performance System**—Cold water inlet sediment reducing device helps prevent sediment build up in tank. Increases first hour delivery of hot water while minimizing temperature build up in tank.
- **Vitraglas[®] Lining**—Bradford White tanks are lined with an exclusively engineered formula that provides superior protection from the highly corrosive effects of hot water. This formula (Vitraglas[®]) is fused to the steel surface by firing at a temperature of over 1600°F.
- **2" Non-CFC Foam Insulation**—Covers the sides and top of the tank, reducing the amount of heat loss. This results in less energy consumption, improved operation efficiencies and jacket rigidity.
- **Water Connections**—3/4" NPT factory installed true dielectric fittings extend water heater life and eases installation (M-2-120R has 1" NPT dielectric waterway fittings).
- **Factory Installed Heat Traps**—Design incorporates a flexible disk that reduces heat loss in piping and eliminates the potential for noise generation (Except M-2-120R).
- **Protective Magnesium Anode Rod**—Provides added protection against corrosion for long trouble-free service.
- **Simultaneous and Non-Simultaneous Operation Available**—Simultaneous operation indicates when both elements (if equipped) are being heated at the same time. Non-Simultaneous operation indicates when one element is being heated at a time.
- **Voltages Available**—120V, 208V, 240V, 277V, 480V.
- **Single Phase or Three Phase Operation Available**—277V may only be wired for single phase operation.
- **T&P Relief Valve Included**—All models have special tapping on top of tank.
- **Low Restriction Brass Drain Valve**—Durable tamper proof design.
- **Design evaluated by UL in accordance with Part 280.707(d) of HUD Mobile Home Construction and Safety Standards for Energy Efficiency.**



6 or 10-Year Limited Tank Warranties / 6 or 10-Year Limited Warranty on Component Parts.

For more information on warranty, please visit www.bradfordwhite.com

For products installed in USA, Canada and Puerto Rico. Some states do not allow limitations on warranties. See complete copy of the warranty included with the heater.

Residential Electric Water Heater

Upright Energy Saver Models

C. E. C. Listed

Model Number	Capacity		Recovery 90°F Rise		A Floor to Heater Top	B Jacket Dia.	C Floor to Water Conn.	D Floor to T&P Conn.	Approx. Shipping Weight
	U.S. Gal.	Imp. Gal.	U.S. GPH*	Imp. GPH*	in.	in.	in.	in.	lbs.
M-2-30R6DS	30	25	21	18	46 ⁷ / ₈	18	48 ¹ / ₈	47 ⁹ / ₁₆	85
M-2-40S6DS	40	33	21	18	46 ⁷ / ₈	20	47 ⁷ / ₈	46 ⁷ / ₈	103
M-2-40T6DS	40	33	21	18	59 ³ / ₄	18	60 ³ / ₄	59 ³ / ₄	110
M-2-50S6DS†	50	42	21	18	46 ¹ / ₂	22	47 ¹ / ₂	46 ¹ / ₂	130
M-2-50T6DS	50	42	21	18	57 ¹ / ₂	20	58 ¹ / ₂	57 ¹ / ₂	123
M-2-65R6DS	65	54	21	18	59 ¹ / ₄	22	60 ¹ / ₄	59 ¹ / ₄	156
M-2-80R6DS	80	67	21	18	59 ¹ / ₄	24	60 ¹ / ₄	59 ¹ / ₄	183
M-2-120R6DS	119	99	21	18	62 ³ / ₄	28	64 ¹ / ₄	62 ¹ / ₄	305

Model Number	Capacity		Recovery 50°C Rise	A Floor to Heater Top	B Jacket Dia.	C Floor to Water Conn.	D Floor to T&P Conn.	Approx. Shipping Weight
	Liters		Liters/Hour*	mm.	mm.	mm.	mm.	kg.
M-2-30R6DS	114		79	1191	457	1222	1199	39
M-2-40S6DS	151		79	1191	508	1216	1191	47
M-2-40T6DS	151		79	1518	457	1543	1518	50
M-2-50S6DS†	189		79	1181	559	1207	1181	59
M-2-50T6DS	189		79	1461	508	1486	1461	56
M-2-65R6DS	246		79	1505	559	1530	1505	71
M-2-80R6DS	303		79	1505	610	1530	1505	83
M-2-120R6DS	450		79	1594	711	1632	1581	138

†Available with optional hand hole cleanout.

For 10 year models, change suffix "6" to "10".

For single element models change suffix "D" to "S".

(M-2-120 not available as a single element model).


*Based on 4500W/4500W, Non-Simultaneous operation.

Wattage	Recovery ▲ GPH Temperature Rise °F				
	60	80	90	100	120
1500W	10	8	7	6	5
2000W	14	10	9	8	7
2500W	17	13	11	10	9
3000W	21	15	14	12	10
3500W	24	18	16	14	12
4000W	28	21	18	16	14
4500W	31	23	21	19	15
5000W	34	26	23	21	17
5500W	38	29	25	23	19
6000W	41	31	28	25	21

▲(GPH based on Non-Simultaneous operation, when Simultaneous operation the GPH will approximately double.)

Wattage Limitations for Simultaneous Operation	Voltage				
	120V	208V	240V	277V	480V
1500W / 1500W	yes	yes	yes	yes	yes
2000W / 2000W	no	yes	yes	yes	yes
2500W / 2500W	no	yes	yes	yes	yes
3000W / 3000W	no	yes	yes	yes	yes
3500W / 3500W	no	yes	yes	no	no
4000W / 4000W	no	yes	yes	yes	yes
4500W / 4500W	no	yes	yes	yes	yes
5000W / 5000W	no	yes	yes	yes	yes
5500W / 5500W	no	no	yes	no	no
6000W / 6000W	no	no	no	yes	yes

Wattage Limitations for Non-Simultaneous Operation	Voltage				
	120V	208V	240V	277V	480V
1500W / 1500W	yes	yes	yes	yes	yes
2000W / 2000W	yes	yes	yes	yes	yes
2500W / 2500W	yes	yes	yes	yes	yes
3000W / 3000W	yes	yes	yes	yes	yes
3500W / 3500W	no	yes	yes	no	no
4000W / 4000W	no	yes	yes	yes	yes
4500W / 4500W	no	yes	yes	yes	yes
5000W / 5000W	no	yes	yes	yes	yes
5500W / 5500W	no	yes	yes	no	no
6000W / 6000W	no	yes	yes	yes	yes



General

All models UL and CUL listed. These heaters are wired inter-locking (Non-Simultaneous, Single Phase) 240V with two 4500W elements, unless otherwise specified.

All water and electrical connections are 3/4" NPT (19mm), 120 gallon model has 1"(25mm) NPT.

All models certified at 300 psi test pressure (2068 kPa) and 150 psi working pressure (1034 kPa).

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.



For U.S. and Canada field service, contact your professional installer or local Bradford White sales representative.

Sales 800-523-2931 • Fax 215-641-1670 / Technical Support 800-334-3393 • Fax 269-795-1089 • Warranty 800-531-2111 • Fax 269-795-1089

International: Telephone 215-641-9400 • Telefax 215-641-9750 / www.bradfordwhite.com

BRADFORD WHITE-CANADA INC. Sales / Technical Support 866-690-0961 / 905-238-0100 • Fax 905-238-0105 / www.bradfordwhite.com

Built to be the Best™

©2012, Bradford White Corporation. All rights reserved.