



A Moen Incorporated Brand

Capstone™



NSF UPC®



Models:
CA41211 2H Lav with 50/50 waste
CA41213 2H Lav less waste



Two Handle Lavatory

DESCRIPTION

- Metal construction with various finishes identified by suffix
- 1/2" IPS connections
- Includes 50-50 pop-up type waste assembly where noted
- Six (6) individual boxes per master carton
- Features red/blue hot/cold temperature indicators

OPERATION

- Lever style handle
- Hot side: Turn counterclockwise to open (clockwise to close)
- Cold side: Turn clockwise to open (counterclockwise to close)
- Will operate with less than 5 lbs. of torque
- No grasping motion required to operate the faucet handles

FLOW

- Flow is limited to 1.5 gpm max. (5.7L/min) at 60 psi

CARTRIDGE



- Ceramic disc technology
- Non-metallic, non-ferrous, and brass material
- Single body construction for easy replacement

STANDARDS

- Third party certified to WaterSense® CSA B125.1, ASME A112.18.1 and all applicable requirements referenced therein including NSF61/9
- Contains no more than 0.25% weighted average lead content
- Complies with California Proposition 65 and the Federal Safe Water Drinking Act
- ADA for lever handles

WARRANTY – RESIDENTIAL, COMMERCIAL

- Ten year limited warranty against defects in materials and manufacturing workmanship
- Refer to the installation instructions enclosed with each CFG product or call 1-888-450-4910 for complete warranty information



CRITICAL DIMENSIONS

- **Note:** This faucet is designed to be installed through 3 holes, 1" minimum diameter, 4" centers
- Maximum deck thickness 0.875" (22.2 mm)