

2 in (50 mm) through 12 in (300 mm)

Parts List – Standard, Fire-Sealed and End-of-Line Lug Valves

Item No.	Description	Carbon Steel	Stainless Steel
1	Body	ASTM A216 Gr. WCB	ASTM A351 Gr. CF-8M
2	Disc	ASTM A351 Gr. CF-8M	ASTM A351 Gr. CF-8M
3	Shaft	ASTM A564 Type 630 17-4 SS	ASTM A564 Type 630 17-4 SS
4	Pin	ASTM A564 Type 630 17-4 SS	ASTM A564 Type 630 17-4 SS
5	Bearing	PTFE/Fiberglass (■ 316 SS Chrome Plated)	PTFE/Fiberglass (■ 316 SS Chrome Plated)
6	Thrust Bearing	ASTM A564 Type 630 17-4 SS	ASTM A564 Type 630 17-4 SS
7	Thrust Washer	1018 Steel	316 SS
* 8	Packing Set	PTFE Cup and Cone (■ Grafoll)	PTFE Cup and Cone (■ Grafoll)
9	Gland	303 SS	303 SS
10	Adjuster	ASTM A351 Gr. CD4MCu	ASTM A351 Gr. CD4MCu
11	Stud-Adjuster	B8M3 (■ Gr. B-7)	B8M3 (■ Gr. B-7)
12	Nut-Adjuster	Gr. 8 (■ Gr. 2H)	Gr. 8 (■ Gr. 2H)
13	Ground Spring	302 SS	302 SS
14	Retainer Ring	ASTM A516 Gr. 70 Carbon Steel	ASTM A240 Type 316 SS
* 15	Lock Ring	Viton A*	Viton A
* 16	Seat	PFA	PFA
* 17	Seat Energizer	Viton A*	Viton A
18	Seat Ring	1020 Steel	ASTM A240 Type 316 SS
19	Jam Nut	300 Series SS	300 Series SS
* 20	Gasket-Fire Seal	■ Grafoll **	■ Grafoll
* 21	Seat-Fire Seal	■ Inconel X750	■ Inconel X750
22	Capscrew	Chrome Steel	Chrome Steel
*33	Seat	UHMWPE	UHMWPE

Note: 2 in (50 mm) through 8 in (200 mm) have 2 upper and 1 lower bearing, 10 in (250 mm) and 12 in (300 mm) have 3 upper and 2 lower bearings as standard. All Fire Sealed have 1 upper and 1 lower bearing.

* Registered trademark of DuPont Company.

** Registered trademark of Union Carbide.

■ Standard for Fire-Sealed

* Recommended spare parts.