
GLOBE IB413T
BRONZE
150 lb. SWP-300 lb. WOG† • Heavy Duty Service • Teflon Disc
Union Bonnet • Gland Packed • Threaded Ends



SPECIFICATIONS

IB413T	**Conforms to: MSS SP-80. Type 2, Class 150, Threaded Ends.**

MATERIAL LIST

NO.	PART	MATERIAL	SPECIFICATION
1	Body	Bronze	ASTM B 62
2	Bonnet	Bronze	ASTM B 62
3	Disc	Teflon	
4	Stem	Bronze	ASTM B 62
5	Disc Holder	Bronze	ASTM B 16 1/4" to 3/4" ASTM B 62 1" and 3" Incl.
6	Union Bonnet Nut	Bronze	ASTM B 62
7	Packing	Non-Asbestos	Commercial
8	Gland	Brass	ASTM B 124 C37700
9	Packing Nut	Brass	ASTM B 283 C37700
10	Disc Nut	Bronze	Commercial
11	Handwheel	Mall. Iron	Commercial
12	Identification Plate	Aluminum	Commercial
13	Handwheel Nut	Brass	Commercial

DIMENSIONS - INCHES / MILIMETERS

Units	Size	A	B	C
Inches	**1/8**	2 1/16	3 15/16	2
MM	**3.18**	52.40	100.03	50.80
Inches	**1/4**	2 1/16	3 15/16	2
MM	**6.35**	52.40	100.03	50.80
Inches	**3/8**	2 1/16	4 1/4	2
MM	**9.53**	52.40	107.95	50.80
Inches	**1/2**	2 7/16	4 9/16	2 1/2
MM	**12.70**	61.93	115.90	63.50
Inches	**3/4**	2 15/16	5 3/16	2 3/4
MM	**19.05**	74.63	131.78	69.85
Inches	**1**	3 7/16	5 1/2	3 1/8
MM	**25.40**	87.33	139.70	79.38
Inches	**1 1/4**	3 7/8	6 1/4	3 1/2
MM	**31.75**	98.43	158.75	88.90
Inches	**1 1/2**	4 1/2	7 1/8	3 3/4
MM	**38.10**	114.30	180.98	95.25
Inches	**2**	5 3/4	8 7/8	4 3/4
MM	**50.80**	146.05	225.43	120.65
Inches	**2 1/2**	6 3/4	10 5/8	5 1/4
MM	**63.50**	171.45	269.88	133.35
Inches	**3**	8	12 1/8	6
MM	**76.20**	203.20	307.98	152.40

† Non-Shock

Rev. 1

BETTER AT EVERY TURN

HAMMONDVALVE
www.hammondvalve.com

The information presented on this sheet is correct at the time of publication. Hammond Valve reserves the right to change design, and/or material specifications without notice. For the most current information access www.hammondvalve.com

7/03 Printed on recycled paper with soy ink.