

Model YB

BRONZE Y-STRAINER

(59 Series)

Job Name:	Contractor:
Job Location:	P.O. Number:
Engineer:	Representative:
Tag:	Wholesale Distributor:

DESCRIPTION

The Apollo® YB Strainers are designed to protect piping systems and process equipment from unwanted foreign particles with minimum pressure loss.

FEATURES

- 100% American Made
- 100% Factory Pressure Tested
- Self-Aligning Screen Design
- Blowout Ball Valve Option

MATERIAL SPECIFICATIONS

Part Name	Material		
Body	Cast Bronze, ASTM B584		
UL Body	Cast Bronze; ASTM B61		
Cap (1/8 – 1")	Brass, ASTM B16		
(1-1/4" – 4")	Bronze, ASTM B584		
Screen	302 Stainless Steel		
O-Ring 1/8" – 1/2"	Teflon®		
Gasket 3/4" - 4"	PTFE		

PERFORMANCE RATING:

Working pressure (non-shock):

125 PSIG @ 350°F STEAM

400 PSIG @ 150°F WATER, OIL, GAS

MODELS

☐ (59000) FEMALE NPT CONNECTION ☐ (59300) SOLDER CONNECTION ☐ (59400) MALE NPT INLET X FEMALE NPT (3/4"-1") ☐ (59UL) UL LISTED (1/8"-1/2" THREADED ONLY)
PTIONS (SUFFIX)

0

☐ (02) - Tapped Cap

☐ (A1) – 40 MESH
(01) - 50 MESH (Standard 1/8" - 1/2")
☐ (B1)- 60 MESH
☐ (C1) - 80 MESH
☐ (H1) - 100 MESH

☐ (P2) - Tapped Cap with Plug \square (06) – Tapped cap with Ball Valve (1/2" – 2" ONLY)

APPROVALS:

CRN 0E8959.5C








PHYSICAL SPECIFICATIONS

Model	Item	Size	Length			Wt.
Number	Number		FNPT	MNPT	SOLDER	(LBS)
YB18	59-000	1/8"	2.0"	Na	Na	.44
YB14	59-001	1/4"	2.0"	Na	Na	.42
YB38	59-002	3/8"	2.69"	Na	Na	.78
YB12	59-003	1/2"	2.69"	Na	2.75"	.75
YB34	59-004	3/4"	3.87"	4.87"	4.0"	1.7
YB1	59-005	1"	4.75"	5.12"	4.75"	2.7
YB114	59-006	1-1/4"	5.12"	Na	5.25"	3.4
YB112	59-007	1-1/2"	5.75"	Na	6.0"	5.3
YB2	59-008	2"	6.75"	Na	7.25"	7.2
YB212	59-009	2-1/2"	7.9"	Na	Na	11.3
YB3	59-010	3"	9.12"	Na	Na	15.5
YB4	59-011	4"	11.9"	Na	Na	30.7

Model number and item number shown are for female NPT connections.



Conbraco Industries, Inc. 701 Matthews Mint Hill Rd. Matthews NC 28106 USA; www.apollovalves.com; 704-841-6000