





ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	2	58403		1/2 THD PROTECTOR	POLYETHYLENE
2	1	58145	9205	BEARING RING	AMPCO ALUM BRONZE
3	1	20499	57044	BODY	A105
4	1	30147	35003	BONNET	A105
5	4	50221	60684A	FINISHED HEX NUT	F594 304SS
6	1	55002	45706B	GASKET	304/GRAFOIL
7	1	32610	17897	GATE	A479 TYPE 410
8	1	35007	53763	HANDWHEEL	MALLEABLE IRON
9	1	50005	17901	HANDWHEEL NUT	A105
10	4	50026	45417A	HEX HD BOLT	A193 GR B7
11	1	40367	28297	NAME PLATE(GREEN)	ALUMINUM
12	1	55175		PACKING	FLEXIBLE GRAPHITE
13	1	34070	35005	PACKING GLAND	A105
14	2	32096	16186	SEAT RING	A479 T410 HF
15	1	32712	28407	STEM	A479 TYPE 410
16	2	50120	21912	STUD BOLT	F593 304SS
17	1	58452		TACK WELD	(RMPWPS555)
18	1	34011	35004	YOKE	A105
19	1	58097	17898	YOKE NUT	A582 TYPE 416

NOTE:

GATE VALVE TO BE TESTED PER API-598 PER RMPVFLT003

X.XX Inches
[XX,X] MM

WEIGHT	5.0 LBS	2.25 Kg
Cv FACTOR		9.6

CNS	57431
REV	31
BY	R. JACKSON
DATE	10-27-2003

DWN BY	JOE CECIL
CHK BY	S.R.
RVD BY	
DATE	1-17-57
SCALE	1.250

31

SERIES No: 13111-04	
ITEM No: 201015	
RATING: 1975 PSI • 100 F	SPECS: API 602/ASME B16.34
BODY A105 SEAT HF DISC 13CR STEM 13CR	
FLOWERVE Vogt Valves	
SULPHUR SPRINGS, TEXAS, USA	
1/2 GATE VALVE - FULL PORT - F.S. OS&Y- BOLTED BONNET - BOLTED GLAND- 5° RENEWABLE SEATS - LOOSE SLOTTED GATE- THREADED ENDS -CLASS 800	
34873-A	