
34873A1



ITEM	QTY	ITEM NO	DRAWING	PART NAME	MATERIAL
1	2	58403		1/2 THD PROTECTOR	POLYETHYLENE
2	1	58145	9205	BEARING RING	AMPCO ALUM BRONZE
3	1	20498	57044	BODY	A182 F316/316L
4	1	30145	35003	BONNET	A182 F316/316L
5	4	50221	60684A	FINISHED HEX NUT	F594 304SS
6	1	55003	45706B	GASKET	316/GRAFOIL
7	1	32612	17897	GATE	A182 T316
8	1	35007	53763	HANDWHEEL	MALLEABLE IRON
9	1	50005	17901	HANDWHEEL NUT	A105
10	4	50036	45417A	HEX HD BOLT	A193 B8M CL 2B
11	1	40448	28297	NAME PLATE(BLUE)	ALUMINUM
12	1	55175		PACKING	FLEXIBLE GRAPHITE
13	1	34069	35005	PACKING GLAND	A182 F316
14	2	32099	16186	SEAT RING	A182 T316L HF
15	1	32715	28407	STEM	A182 T316
16	2	50120	21912	STUD BOLT	F593 304SS
17	1	TW-33		TACK WELD	(RMPWPS369)
18	1	34010	35004	YOKE	A182 F316
19	1	58097	17898	YOKE NUT	A582 TYPE 416

SERIES No:	12401-04
ITEM No:	200875
RATING: 1920 PSI • 100 F	SPECS: API 602/ASME B16.34
BODY F316 | SEAT 316 HF | DISC 316 | STEM 316	

NOTE:

.

GATE VALVE TO BE TESTED PER API-598 PER RMPVFLT003

X.XX Inches
[XX,X] MM

WEIGHT	5.0 LBS	2.26 Kg
Cv FACTOR		9.6

CNS	57431
REV	31
BY	R.JACKSON
DATE	10-27-2003

DWN BY	JOE CECIL
CHK BY	S.R.
RVD BY	
DATE	1-17-57
SCALE	1.250

31

FLOWSERVE Vogt Valves

SULPHUR SPRINGS, TEXAS, USA

1/2 GATE VALVE - FORGED STEEL
OS&Y- BOLTED BONNET - BOLTED GLAND-
5° RENEWABLE SEATS - LOOSE SLOTTED GATE-
THREADED ENDS -CLASS 800

34873A1

34873