

50GB SERIES

BRONZE GAS SHUT-OFF BALL VALVE

Job Name:	Contractor:
Job Location:	P.O. Number:
Engineer:	Representative:
Тад:	Wholesale Distributor:

DESCRIPTION

The Apollo® GB-50 series bronze ball valves are designed with proven ASTM grade corrosion resistant materials for "main burner" applications, with cast-in single or dual pilot taps for faster, simpler installation. Options include a die-cast zinc "wing" or "tee" handle.

FEATURES

- Rated Gas Pressures of ½ and 5 psig
- · Full port design ensures maximum capacity
- Reversible Steel Lever Handle
- For natural gas, manufactured and mixed gases, • LP gas and LP gas-air mixtures
- Wing and Tee Handle options •
- UL 125 and UL 842 listed
- 100% factory tested
- Made In USA

MATERIAL

Part Name	Material				
Body	ASTM B584 Bronze				
Ball	ASTM B16 Brass, Cr PLT				
Stem Packing	RPTFE				
Seat	PTFE				
Stem/Gland	ASTM B16 Brass				
Retainer	ASTM B16 Brass				
Handle / Nut	Steel, Zn PLT, Plastisol Grip				

CAPACITIES AND DIMENSIONS

Single Tapped	Size (in)	Side Tap	Port	A	в	c	D	BTU/hr
50GB301	1⁄2"	1/8"	0.5	2.25	1.68	3.85	1.00	693,000
50GB401	3⁄4"	1/8"	0.75	2.67	1.93	3.85	1.12	1,258,000
50GB501	1"	1/8"	1	3.42	2.19	4.78	1.53	3,144,000
50GB601	1¼"	1/8"	1.25	3.86	2.37	4.78	1.62	3,250,000
50GB701	1½"	1/8"	1.5	4.22	2.81	5.40	1.81	7,745,000
50GB801	2"	1/8"	2	5.02	3.18	5.40	2.18	14,741,000
50GB5A1	1"	1/4"	1	3.42	2.19	4.78	1.53	3,144,000
50GB6A1	1¼"	1/4"	1.25	3.86	2.37	4.78	1.62	6,441,000
50GB7A1	1½"	1/4"	1.5	4.22	2.81	5.40	1.81	7,745,000
50GB8A1	2"	1/4"	2	5.02	3.18	5.40	2.18	14,741,000

Note: Capacities based on 1000 BTU/cubic feet gas at 0.64 specific gravity, at a P.D. of 1" W.C.

Specify suffix -A for dual tapped version. 1/2" not available dual tapped.





GB50-A

ISO 900

OPTION


- 1/8" Side Tap Standard
- 1/4" Side Tap (1" and larger)
- Dual Tap (¾" and larger) –A Suffix
- Tee Handle



APPROVALS

- ANSI Z21.15, CGA 9.1 (1/2 psig Service) indoor gas shutoff
- ASME B16.44 (5 psig Service)
- MSS SP-10; Ball Valves
- Federal Specification: WW-V-35C, Type: II
- Canadian Registration Number: 0C10908.5C
- Guide YRPV: Gas Shut-Off Valve for use with natural and manufactured gases
- Guide YSTD: LP Gas shut-off valve
- Guide YRBX: Flammable liquid shutoff valve
- Guide MHKZ: No. 6 oil at 250°F





Conbraco Industries, Inc. 701 Matthews Mint Hill Rd. Matthews NC 28105 USA ; www.apollovalves.com ; 704-841-6000

Conbraco Industries can accept no responsibility for possible errors in this document and reserves the right to alter its product design or construction without notice and without incurring any obligation to make such changes on Contraco products previously or subsequently sold. All product specifications are approximate and are provided for reference only.