

Two Piece Gas Ball Valves

Product Features

- · Heavy forged brass body
- · Working temperature: 175°F
- 5 psig
- All models certified by Canadian Gas Association
- . Threaded ends comply with ANSI B2.1
- ISO 9000 certified manufacturer
- AGA design certified and tested to ANSI Z21.15-1989
- · Not for use at or below ground level




PFR602MDC

No.	Part Name	Quantity	
1	Screw	1	
2	Handle	1	
3	Stem	1	
4	Stem Gland Screw	1	
5	Gland packing	1	
6	Name Plate	1	
7	Body	1	
8	Ball Disc Teflon	1	
9	Ball Disc	1	
10	End Plug	1	
11	Thread Cover*	1	
*PFR602FLD has Qty 2			

Model	Size	- 1	D
INIUUGI	0126	_	ע
PFR602MDC	3/8" Flare x 1/2" Male	2.48"	0.39"
	1	2.48" 2.44"	

Product Specifications



Warranty and Codes

This PROFLO product carries a 1-year limited warranty.



