

## 3 Piece Process/Instrumentation, 60 Series


**Part No.**

SS-62TF4

**Part Description:**

SS 3-Piece 60 Series Ball Valve, Reinforced PTFE Seats, 1/4 in. FNPT

## Product Specifications

General	
Flow Pattern	Straight (2-way)
Service Class	General
Size	1/4 in. Nominal - 62 Series
Valve Material	Stainless Steel
End Connection 1 Size	1/4 in
End Connection 1 Type	Female NPT
End Connection 2 Size	1/4 in
End Connection 2 Type	Female NPT
Handle Color	Black
Handle Style	Lever
Approval	No Approval
Ball/Stem Material	Stainless Steel
Cleaning	Swagelok® Standard cleaning SC-10
Fastener Material	316 Stainless Steel
Flange Seal Material	Fluorocarbon FKM
ID Tag	No
Laser Etch	No
Low Dead Space Insert	No
Lubricant	Dow111 and WL8
Packing	Reinforced PTFE
Seat Material	Reinforced PTFE
Seat Spring Material	316 Stainless Steel
Stem Bearing Material	Alloy X750
Testing	Testing according to WS-22
Max Temperature Pressure Rating	450°F @ 100 PSIG /232°C @ 6.8 BAR
Room Temperature Pressure Rating	2200 PSIG @ 100°F /151 @ BAR 37°C

! The complete catalog contents must be reviewed to ensure that the system designer and user make a safe product selection. When selecting products, the total system design must be considered to ensure safe, trouble-free performance. Function, material compatibility, adequate ratings, proper installation, operation, and maintenance are the responsibilities of the system designer and user.

 Caution: Do not mix or interchange valve components with those of other manufacturers.

© 2013 Swagelok Company